

Height-adjustable material stands - in increments and tilting

Application:

For providing materials in plastic and sheet steel boxes, wire baskets etc. directly at workstations.

Execution:

- Profile steel/tube construction with sheet steel platform
- Sheet steel platform with support edge on one side
- Platform tilts by 15° and 30°
- Height-adjustable in increments of 25 mm

Delivery:

Disassembled



Art. no.	50261 015
Brand	FETRA
Manufacturer Part Number	1891
Material of loading surface	Steel plate
Suitable for transporting	Electrical components
Load-carrying capacity	150 kg
Number of loading surfaces	1
Loading surface size	510 x 410 mm
ESD-capable	Yes
Number of fixed rollers	0
Number of steering rollers	4 PCS
With wheel lock	Yes
Total stop optional	No
Wheel width	25 mm
Wheel diameter	75 mm
Material of wheel	TPE-ESD
Colour	Slate grey RAL 7015
Surface	Powder-coated
Gross Weight	16.000 kg
Product Group	5AB

EAN

4017976018911