




Datasheet

RS PRO POLYTETRAFLUOROETHYLENE PTFE SERIES

Stock number: See Table

EN



1. Polytetrafluoroethylene

Extruded from chemically inert compound, PTFE thin walled tubing is used in a wide range of applications, Aerospace, Medical and Chemical.

Key Features:

- Excellent resistance to chemicals.
- Excellent temperature range -60°C to +250°C.
- Excellent co-efficiency of friction.
- FDA approved.
- Excellent weathering properties.
- Excellent electrical insulation properties.

Sizes:


50m and 100m lengths
Other sizes and coil lengths available upon request

Colours:

Natural

Applications:

- Pneumatic control system
- Fuel and lubrication lines
- Chemical transfer tubing



Product Ref	Internal Diameter	External Diameter	Minimum Burst Pressure	Coil Length
1860591	4mm	6mm	84 Bar	50m
1860592	6mm	8mm	56 Bar	50m
1860593	8mm	10mm	42 Bar	50m
1860595	10mm	12mm	34 Bar	50m