

MECANICAL HYGROSTAT PERMANENTLY
ADJUSTED KFR 012 50% RF



Figure similar

Model		
product brand name		SIVACON
Design of the switching function		CO contact
Electricity		
Current / Rated value	A	5
Main circuit		
Operating voltage / Rated value		
• minimum	V	120
• maximum	V	250
Adjustable parameters		
Adjustable response value relative humidity / initial value	%	50
Adjustable response value relative humidity / Full-scale value	%	50
Product details		
Product component / digital display		No
Mechanical Design		
Mounting type		terminal mounting
Certificates		
Equipment marking		
• acc. to DIN EN 61346-2		K
• acc. to DIN EN 81346-2		K



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR21703C>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR21703C/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR21703C

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015