

MTEN clamp holder, negative, neutral

For copy and longitudinal turning with TN indexable insert

ATORN[®]

Application

For copy and longitudinal turning with TN indexable insert, 60°.

Version

- Precision-manufactured steel support, burnished, hardened, adjustable clamping system, type T, working angle 93°, tip angle 60°, clearance angle 0°

Advantage

- Triple-edge geometry lowers cost per cut
- Negative geometry of the body ensures good stability and force absorption at large cutting depths
- Broad range of use: suitable for both finishing and roughing operations
- Adjustable clamp minimises vibrations and ensures good force transfer



Art. No.	17859 001
ISO name	MTEN N 2020 K16
Shaft height	20 mm
Shank width	20 mm
Length	125 mm
Programming size	10.5 mm
Length of head	34 mm
Suitable for indexable inserts	TN.. 1604..
Tool design	Neutral
DIN	4983

EAN-Code

4050293 127843