

Product information

14 26 160

Diagonal Insulation Stripper

IEC 60900 DIN EN 60900

- With long cutter
- High cutting capacity due to high leverage joint
- Precision stripping holes for single conductors of 1.5 and 2.5 mm²
- Convenient cutting of NYM cables up to 5 x 2.5 mm²
- Long tips for ultra fine cutting work also in confined areas
- Induction-hardened precision blades, cutting edge hardness approx. 60 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



⚡ 1000V 

General	
Article No.	14 26 160
EAN	4003773040279
Pliers	chrome-plated
Head	chrome-plated
Handles	insulated with multi-component grips, VDE-tested
Weight	216 g
Dimensions	160 x 60 x 30 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities soft wire (diameter)	Ø 2.5 mm
Cutting capacities medium hard wire (diameter)	Ø 1.5 mm
Stripping capacities in square millimetres	1.5 / 2.5 mm ²
AWG	16 / 14
VDE tested	yes

technical change and errors excepted

