

### Product type designation

### RF360T transponder

SIMATIC RF300 TRANSPONDER RF360T EPOXY-CARD, 32 KBYTE FRAM, IP 67, -25 UP TO +70 DGR/C, 85 X 54 X 2.5 MM, MIN. ORDER QUANTITY 10 PCS



Figure similar

### Wireless frequencies

Operating frequency / Rated value	13.56 MHz
-----------------------------------	-----------

### Electrical data

Range / maximum	150 mm; range is reader dependent: observe <a href="http://support.automation.siemens.com/WW/view/en/67384964">http://support.automation.siemens.com/WW/view/en/67384964</a>
Protocol / with radio transmission	RF300-specific
Transfer rate / with radio transmission / maximum	106 kbit/s
Product property / multitag-capable	Yes
Product component / Backup battery	No

### Memory

Type of memory	FRAM/EEPROM
Storage capacity / of the user memory	32765 byte
Type of memory organization	UID (fixed code) 4 bytes, user memory 32765 bytes, OTP memory 20 bytes
Number of read cycles / at ambient temperature < 40 °C / maximum	10000000000
Number of write cycles / at ambient temperature < 40 °C / maximum	10000000000
Data retention time / at ambient temperature < 40 °C / not less than	10 y
Property of memory	Block-by-block write protection of the OTP memory

### Mechanical data

Material	Epoxy resin
Color	anthracite

Mounting distance / relating to metal surfaces / recommended / minimum	20 mm
--	-------

### Permitted ambient conditions

Ambient temperature	
<ul style="list-style-type: none"> <li>during read/write access</li> </ul>	-25 ... +75 °C
<ul style="list-style-type: none"> <li>outside the read/write area</li> </ul>	-40 ... +85 °C
<ul style="list-style-type: none"> <li>during storage</li> </ul>	-40 ... +85 °C
Protection class IP	IP67
Shock resistance	According to DIN EN 60721-3-7 Class 7 M3
Shock acceleration	500 m/s <sup>2</sup>
Resistance against vibration	200 m/s <sup>2</sup>
Resistance to mechanical stress	Continuous torsion and bending stress not permissible

### Design, dimensions and weight

Width	55 mm
Height	2.5 mm
Depth	86 mm
Net weight	25 g
Mounting type	2 x M3 screws, mounting bag (see accessories)

### Product properties, functions, components / general

Product property	
<ul style="list-style-type: none"> <li>silicon-free</li> </ul>	Yes
<ul style="list-style-type: none"> <li>printable</li> </ul>	No

### Standards, specifications, approvals

MTBF	1200 y
------	--------

### Accessories

accessories	Fixing strap, spacer
-------------	----------------------

### Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> <li>to website: Selector SIMATIC NET SELECTION TOOL</li> </ul>	<a href="http://www.siemens.com/snst">http://www.siemens.com/snst</a>
<ul style="list-style-type: none"> <li>to website: Industrial communication</li> </ul>	<a href="http://www.siemens.com/simatic-net">http://www.siemens.com/simatic-net</a>
<ul style="list-style-type: none"> <li>to website: Industry Mall</li> </ul>	<a href="https://mall.industry.siemens.com">https://mall.industry.siemens.com</a>
<ul style="list-style-type: none"> <li>to website: Information and Download Center</li> </ul>	<a href="http://www.siemens.com/automation/net/catalog">http://www.siemens.com/automation/net/catalog</a>
<ul style="list-style-type: none"> <li>to website: Image database</li> </ul>	<a href="http://automation.siemens.com/bilddb">http://automation.siemens.com/bilddb</a>
<ul style="list-style-type: none"> <li>to website: CAx Download Manager</li> </ul>	<a href="http://www.siemens.com/cax">http://www.siemens.com/cax</a>
<ul style="list-style-type: none"> <li>to website: Industry Online Support</li> </ul>	<a href="https://support.industry.siemens.com">https://support.industry.siemens.com</a>
<b>last modified:</b>	09.03.2015