

CopyMax® die-sinking cutter, conical

For indexable milling inserts CMR .. SR/DR


KIENINGER

Application:

The CopyMax family has been specially developed for die and mould making. With the CopyMax® 1 one-sided indexable insert and CopyMax® 2 with two fully functional blades, the customer can optimise savings potential according to the requirements of the component. The system demonstrates its qualities in particular during rough machining and in the subsequent semi-finishing process. Both tools are produced in the HQS (High Quality Sintering) manufacturing process and have precision-sintered cutting edges.

Execution:

- Steel shank
- For round indexable milling inserts
- Conical neck



Art. no.	16123 216
Brand	KIENINGER
Manufacturer Part Number	7142056
Cutting edge diameter	16 mm
Clearance length	55 mm
Length	120 mm
Shank diameter	20 mm
Material	Steel
Gross Weight	0.160 kg
Product Group	1K2