

## General Information

|                               |   |
|-------------------------------|---|
| <b>Extended Product Type:</b> | ZK6-PE  |
| <b>Product ID:</b>            | 1SNK708150R0000   |
| <b>EAN:</b>                   | 3472597081507   |
| <b>Catalog Description:</b>   | ZK6-PE PI-Spring clamp Terminal Block - Ground - Green Yellow   |
| <b>Long Description:</b>      | Improve the safety of your installation in the event of a short-circuit thanks to our screwless rail contact: - Rail contact non operator dependent, - Performances above the requirements of the IEC 60947-7-2 terminal block standard, - Secured snap on or off the rail, - Profile aligned with ZK6. |

## Ordering

|                                |              |
|--------------------------------|--------------|
| <b>Color:</b>                  | Green-Yellow |
| <b>Minimum Order Quantity:</b> | 20 piece     |
| <b>Customs Tariff Number:</b>  | 85369010     |

## Popular Downloads

|   |                 |
|---|-----------------|
| <b>Data Sheet, Technical Information:</b> | 1SNK162030D0201 |
| <b>Instructions and Manuals:</b>          | 1SNK160027C0201 |

## Dimensions

|                                    |         |
|------------------------------------|---------|
| <b>Product Net Width:</b>          | 8 mm    |
| <b>Product Net Height:</b>         | 64.6 mm |
| <b>Product Net Length:</b>         | 42 mm   |
| <b>Product Net Depth / Length:</b> | 42 mm   |
| <b>Product Net Weight:</b>         | 20.3 g  |

## Technical

|  |   |
|--|---|
| <b>Rated Cross-Section:</b>              | 6 mm <sup>2</sup>   |
| <b>Spacing:</b>                          | 8 mm  |
| <b>Connection Type:</b>                  | PI Spring   |
| <b>Function:</b>                         | Ground  |
| <b>Number of Levels:</b>                 | 1   |
| <b>Connecting Capacity Main Circuit:</b> | Spring Clamp / Flexible 1x 0.5 ... 6 mm <sup>2</sup><br>Spring Clamp / Rigid 1x 0.5 ... 10 mm <sup>2</sup><br>Spring Clamp / With Insulated Ferrule 1x 0.5 ... 6 mm <sup>2</sup><br>Spring Clamp / Without Insulated Ferrule 1x 0.5 ... 6 mm <sup>2</sup> |
| <b>Gauge Type:</b>                       | A5 & 3.9 mm Dia.  |

|  |  |
|--|--|
| <b>Rated Short-time Withstand Current (<math>I_{cw}</math>):</b> | for 1 s 720 A  |
| <b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>   | 8000 V   |
| <b>Dielectric Test Voltage:</b>                                  | 2200 V   |
| <b>Pollution Degree:</b>   | 3  |
| <b>Degree of Protection:</b>                                     | acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20   |
| <b>Insulation Material:</b>                                      | Polyamide  |
| <b>Mounting on DIN Rail:</b>                                     | TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715<br>TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 |
| <b>Wire Stripping Length:</b>                                    | 12.5 mm  |

## Technical UL/CSA

|   |   |
|---|---|
| <b>Connecting Capacity Main Circuit UL/CSA:</b> | Spring Clamp / Rigid 1x 24 ... 8 AWG<br>Spring Clamp / With Insulated Ferrule 1x 24 ... 10 AWG<br>Spring Clamp / Without Insulated Ferrule 1x 24 ... 10 AWG |
| <b>Connecting Capacity UL/CSA:</b>              | Stranded 8 AWG  |
| <b>Flammability According to UL94:</b>          | V0  |

## Environmental

|  |  |
|--|--|
| <b>Ambient Air Temperature:</b>                        | Operation -55 ... +110 °C<br>Storage -55 ... +110 °C |
| <b>Resistance to Vibrations acc. to IEC 60068-2-6:</b> | Compliant  |
| <b>RoHS Status:</b>                                    | Following EU Directive 2011/65/EU                    |

## Certificates and Declarations (Document Number)

|  |                 |
|--|-----------------|
| <b>ATEX Certificate:</b>               | 1SND162009A1702 |
| <b>BV Certificate:</b>                 | 1SND162013A0203 |
| <b>CB Certificate:</b>                 | 1SND162017A0200 |
| <b>CSA Certificate:</b>                | 1SND162014A0206 |
| <b>cUL Certificate:</b>                | 1SND162012A0204 |
| <b>Declaration of Conformity - CE:</b> | 1SND225112U1004 |
| <b>DNV Certificate:</b>                | 1SND162023A0200 |
| <b>EAC Certificate:</b>                | 1SND161010A1100 |
| <b>Environmental Information:</b>      | 1SND220072E1002 |
| <b>Instructions and Manuals:</b>       | 1SNK160027C0201 |
| <b>RoHS Information:</b>               | 1SND230535F0201 |

## Classifications

|                                    |   |
|------------------------------------|---|
| <b>Object Classification Code:</b> | X |
|------------------------------------|---|

**ETIM 4:** EC000901 - Ground terminal block

---

**ETIM 5:** EC000901 - Ground terminal block

---

**ETIM 6:** EC000901 - Ground terminal block

## Container Information

**Package Level 1 Units:** 20 piece

---

**Package Level 1 Width:** 82 mm

---

**Package Level 1 Depth / Length:** 130 mm

---

**Package Level 1 Height:** 44 mm

---

**Package Level 1 Gross Weight:** 0.426 kg

---

**Package Level 1 EAN:** 3472597081507

---

**Package Level 2 Units:** 480 piece

---

**Package Level 2 Width:** 300 mm

---

**Package Level 2 Depth / Length:** 400 mm

---

**Package Level 2 Height:** 200 mm

---

**Package Level 2 Gross Weight:** 10.224 kg

---

**Package Level 3 Units:** 23040 piece

---

**Product Packing Type:** Box

