

T-slot bolts



Application:

For clamping workpieces on machine tables.

Execution:

- Tempered
- Rolled thread
- Forged
- With milled groove guide
- M8 to M12, strength class 10.9
- M16 to M24, strength class 8.8
- DIN 787



Art. no.	26200 550
Brand	AMF
Manufacturer Part Number	85779
DIN	787
Thread dimension	M16
Groove width	16 mm
Length excluding head	200 mm
Outer diameter	15.7 mm
Thread length	125 mm
Length of head	25 mm
Head height	9 mm
Gross Weight	0.423 kg
Product Group	260

EAN

4020772085773