

INDIGA flat files

Type 9010

LAPPORT
SCHLEIFTECHNIK

Application:

For sharpening and reworking tools for wood, metal and plastic processing, e.g. scrapers, machine and plane knives, steels, reamers and gauges as well as measuring instruments.

Execution:

- Best used with thin-bodied oil, petroleum or water
- Machined and wetted on all sides after burning

Advantage:

- High endurance and grinding force



| | |
|---|-------------------|
| Art. no. | 69346 340 |
| Brand | LAPPORT |
| Manufacturer Part Number | 100606 |
| Binding | Ceramically bound |
| Surface structure | Fine |
| Grid size | 400 |
| Form | Flat |
| Length | 150 mm |
| Width | 16 mm |
| Thickness | 8 mm |
| Number of pieces per packet | 3 PCS |
| Material of abrasive medium | Corundum |
| Suitable for finishing | 2 - suitable |
| Suitable for main machining | 2 - suitable |
| Suitable for surface inspection | 3 - less suitable |
| Suitable for surface care | 2 - suitable |
| Suitable for material rubber | 3 - less suitable |
| Suitable for material cast iron | 2 - suitable |
| Suitable for material HSS | 3 - less suitable |
| Suitable for material carbide | 3 - less suitable |
| Suitable for material ceramic | 3 - less suitable |
| Suitable for material plastics | 3 - less suitable |
| Suitable for material non-ferrous metals | 3 - less suitable |
| Suitable for material steel (hardened) | 2 - suitable |
| Suitable for material steel (unhardened) | 1 - very suitable |
| Suitable for material tool steel | 2 - suitable |
| ISO | 525 |
| Length x width | 150 x 16 mm |
| Length x width x thickness | 150 x 16 x 8 mm |
| Type description | Corundum |
| Gross Weight | 0.010 kg |
| Product Group | 6HL |