

# AJ

## 2100-2400VA



Model	AJ 2100-12	AJ 2400-24	
<b>Inverter</b>			
Nominal battery voltage	12 Vdc	24 Vdc	
Input voltage range	10.5 – 16 Vdc	21–32 Vdc	
Continuous power @ 25°C	2000 VA	2000 VA	
Power 30 min. @ 25°C	2100 VA	2400 VA	
Power 5 min. @ 25°C	2450 VA	2800 VA	
Power 5 sec. @ 25°C	5000 VA	5200 VA	
Asymmetric load	1000 VA	1200 VA	
Max. efficiency (%)	92 %	94%	
Cos φ max.	0.1 – 1 up to 2000 VA	0.1 – 1 up to 2000 VA	
Detection of the load	Adjustable: 1 → 20 W		
Short-circuit current AC 2 sec.	26 Aac (52 Aac*)	30 Aac (60 Aac*)	
Output voltage	Sine wave 230 Vac (120 Vac*) ±5 %		
Frequency	50 Hz (60 Hz*) ± 0.05 % (crystal controlled)		
Distortion THD (resistive load)	< 3 % (@ Pnom. & Uin nom.)	< 3% (@ Pnom & Uin nom.)	
Consumption Stand-by	0.7 W	1.2 W	
Consumption «ON» no load	16 W	16 W	
Overheat protection (±5°C)	Shut down @ 75°C - Auto-restart @ 70°C		
Short circuit protection	Automatic disconnection with 2 time restart attempt		
Reverse polarity protection by internal fuse	Not protected	150 A	
Deep discharge battery protection	Shut off @ 0.87 x Unom - Automatic restart @ Unom		
Max. battery voltage	Shut off @ >1.33 x Unom - Automatic restart @ < Umax		
Acoustic alarm	Before low battery or overheating disconnection		
<b>General data</b>			
Weight	19 kg	18 kg	
Dimensions h/w/l [mm]	273 / 399 / 117		
Protection index IP	IP 20 conforms to DIN 40050		
Certification ECE-R 10 (E24)	•	•	
EU declaration of conformity	<b>Low Voltage Directive (LVD) 2014/35/EU:</b> - EN 62109-1:2010  <b>Electromagnetic Compliance (EMC) Directive 2014/30/EU:</b> - EN 61000-6-2:2005, EN 61000-6-4:2007 / A1:2011		
Operating temperature	-20°C to +50°C		
Relative humidity in operation	95 % without condensation		
Ventilation forced	From 45°C ± 5°C		
Acoustic level	< 45 dB (with ventilation)		
Warranty	5 years		
ISO Certification	9001:2008 / 14001:2004		
Approximate correction of Pnom	-1.5 % / °C since + 25°C		
Recommended battery capacity	> 5 x Pnom/Unom (recommended value in Ah)		
Length cables (Battery/AC out)	1.7m / 1m		
<b>Options</b>			
Solar regulator	Voltage max.	AJ 2100-12-S: 25 Vdc	AJ 2400-24-S: 45 Vdc
	Current max.	30 Adc	
	Principle	Floating 3 stages (I/U/UO)	
	Absorption voltage	14.4 Vdc	28.8 Vdc
	Floating voltage	13.6 Vdc	27.2 Vdc
<b>Accessories</b>			
JT8 Remote control	•		

\* 120Vac/60Hz on request

\*\* Standby with solar option -S

Data may change without any notice

# AJ series



Model	AJ 275-12	AJ 350-24	AJ 400-48	AJ 500-12	AJ 600-24	AJ 700-48	
<b>Inverter</b>							
Nominal battery voltage	12Vdc	24Vdc	48Vdc	12Vdc	24Vdc	48Vdc	
Input voltage range	10.5 – 16Vdc (24Vdc max.)	21 – 32Vdc (44Vdc max.)	42 – 64Vdc (64Vdc max.)	10.5 – 16Vdc (24Vdc max.)	21 – 32Vdc (44Vdc max.)	42 – 64Vdc (64Vdc max.)	
Continuous power @ 25°C	200VA	300VA	300VA	400VA	500VA	500VA	
Power 30 min. @ 25°C	275VA	350VA	400VA	500VA	600VA	700VA	
Power 5 min. @ 25°C	350VA	500VA	600VA	575VA	675VA	900VA	
Power 5 sec. @ 25°C	450VA	650VA	1000VA	1000VA	1200VA	1400VA	
Maximum asymmetric load	150VA	150VA	200VA	250VA	300VA	300VA	
Max. efficiency (%)	93%	94%	94%	93%	94%	94%	
Cos φ max.	0.1 – 1 up to 200 VA	0.1 – 1 up to 300 VA	0.1 – 1 up to 300 VA	0.1 – 1 up to 400VA	0.1 – 1 up to 500VA	0.1 – 1 up to 500VA	
Detection of the load	2W (only with the solar option -S)			Adjustable: 1 - 20W			
Current of short-circuit 2 sec. (exit)	2.3Aac (4.6Aac*)	3.2Aac (6.4Aac*)	4.6Aac (9.2Aac*)	5.2Aac(10.4Aac*)	5.7Aac (11.4Aac*)	7Aac (14Aac*)	
Output voltage	Sine wave 230Vac (120Vac*) ±5%						
Frequency	50Hz (60Hz*) ± 0.05% (crystal controlled)						
Distortion THD (resistive load)	< 5% (@ Pnom.)						
Consumption Stand-by	0.3W**	0.5W**	1.1W**	0.4W	0.6W	1.5W	
Consumption « ON » no load	2.4W	3.5W	5.2W	4.6W	7.2W	12W	
Overheat protection (±5°C)	Shut down @ 75°C - Auto-restart @ 70°C						
Overload and short circuit protection	Automatic disconnection with 2 time restart attempt						
Reverse polarity protection by internal fuse	60A	40A	25A	120A	90A	60A	
Deep discharge battery protection	Shut off @ 0.87 x Unom - Automatic restart @ Unom						
Max. battery voltage	Shut off @ >1.33 x Unom - Automatic restart @ < Umax						
Acoustic alarm	Before low battery or overheating disconnection						
<b>General data</b>							
Weight	2.4 kg	2.6 kg		4.5 kg			
Dimensions hxxw (mm)	142x163x84			142x240x84			
Protection index IP	IP 30 conforms to DIN 40050						
Certification ECE-R 10 (E24)	•	•	Not available	•	•	Not available	
EC conformity	EN 61000-6-1, EN 61000-6-3, EN 55014, EN 55022, EN 60950-1						
Operating temperature	-20°C up to +50°C						
Relative humidity in operation	95% without condensation						
Ventilation forced	From 45°C ± 5°C						
Acoustic level	< 45 dB (with ventilation)						
Warranty	5 years						
Approximate correction of Pnom	-1.5%/°C since +25°C						
Recommended battery capacity	> 5 x Pnom/Unom (recommended value in Ah)						
Length cables (Battery/left AC)	1.2m / 1m			1.5m / 1m			
<b>Options</b>							
Solar regulator	Voltage max.	25Vdc	45Vdc	90Vdc	25Vdc	45Vdc	90Vdc
	Current max.	10Adc			15Adc		
	Principle	Floating 3 stages (I/U/UO)					
	Absorption voltage	14.4Vdc	28.8Vdc	57.6Vdc	14.4Vdc	28.8Vdc	57.6Vdc
	Floating voltage	13.6Vdc	27.2Vdc	54.4Vdc	13.6Vdc	27.2Vdc	54.4Vdc
Plug for remote control (RCM)	•	•	•	•	•	•	

\* 120Vac/60Hz on request

\*\* Standby with solar option -S

Data may change without any notice.

Model	AJ 1000-12	AJ 1300-24	AJ 2100-12	AJ 2400-24	
<b>Inverter</b>					
Nominal battery voltage	12Vdc	24Vdc	12Vdc	24Vdc	
Input voltage range	10.5 – 16Vdc (24Vdc max.)	21–32Vdc (44Vdc max.)	10.5 – 16Vdc (20Vdc max.)	21–32Vdc (40Vdc max.)	
Continuous power @ 25°C	800VA	1000VA	2000VA	2000VA	
Power 30 min. @ 25°C	1000VA	1300VA	2100VA	2400VA	
Power 5 min. @ 25°C	1200VA	2000VA	2450VA	2800VA	
Power 5 sec. @ 25°C	2200VA	2800VA	5000VA	5200VA	
Maximum asymmetric load	500VA	600VA	1000VA	1200VA	
Max. efficiency (%)	93%	94%	92% @ 300VA	94% @ 300VA	
Cos φ max.	0.1 – 1 up to 800VA	0.1 – 1 up to 1000VA	0.1 – 1 up to 2000VA	0.1 – 1 up to 2000VA	
Detection of the load	Adjustable: 1 - 20W				
Current of short-circuit 2 sec. (exit)	10Aac (20Aac*)	13Aac (26Aac*)	26Aac (52Aac*)	30Aac (60Aac*)	
Output voltage	Sine wave 230Vac (120Vac*) ±5%				
Frequency	50 Hz (60Hz*) ± 0.05% (crystal controlled)				
Distortion THD (resistive load)	< 5% (@ Pnom. & Uin nom.)				
Consumption Stand-by	0.7W	1.2W	0.7W	1.2W	
Consumption « ON » no load	10W	13W	16W	16W	
Overheat protection (±5°C)	Shut down @ 75°C - Auto-restart @ 70°C				
Short circuit protection	Automatic disconnection with 2 time restart attempt				
Reverse polarity protection by internal fuse	125A	100A	Not protected	150A	
Deep discharge battery protection	Shut off @ 0.87 x Unom - Automatic restart @ Unom				
Max. battery voltage	Shut off @ >1.33 x Unom - Automatic restart @ < Umax				
Acoustic alarm	Before low battery or overheating disconnection				
<b>General data</b>					
Weight	8.5 kg		19 kg	18 kg	
Dimensions hxxw (mm)	142x428x84		273x399x117		
Protection index IP	IP 30 conforms to DIN 40050		IP 20 conforms to DIN 40050		
Certification ECE-R 10 (E24)	•	•	•	•	
EC conformity	EN 61000-6-1, EN 61000-6-3, EN 55014, EN 55022, EN 60950-1				
Operating temperature	-20°C up to +50°C				
Relative humidity in operation	95% without condensation				
Ventilation forced	From 45°C ± 5°C				
Acoustic level	< 45 dB (with ventilation)				
Warranty	5 years				
Approximate correction of Pnom	-1.5%/°C since +25°C				
Recommended battery capacity	> 5 x Pnom/Unom (recommended value in Ah)				
Length cables (Battery/left AC)	1.5m / 1m		1.7m / 1m		
<b>Options</b>					
Solar regulator	Voltage max.	25Vdc	45Vdc	25Vdc	45Vdc
	Current max.	25Adc		30Adc	
	Principle	Floating 3 stages (I/U/UO)			
	Absorption voltage	14.4Vdc	28.8Vdc	14.4Vdc	28.8Vdc
	Floating voltage	13.6Vdc	27.2Vdc	13.6Vdc	27.2Vdc
Remote control JT8 supplied with 5 m cable	•	•	•	•	