

## Standard dial gauges

### Application:

For measuring lengths and length differences, e.g. concentricity, flatness, positional measurements.

### Execution:

- Measuring pin and clamping shaft made from durable stainless steel

### Delivery:

In a case



<b>Art. no.</b>	<b>33080 010</b>
<b>Brand</b>	HK
<b>Manufacturer Part Number</b>	33080010
<b>Length measuring range</b>	10 mm
<b>Scale value</b>	0.01 mm
<b>Measurement travel of one pointer revolution</b>	1 mm
<b>Outer diameter</b>	80 mm
<b>Shock protection</b>	No
<b>Material of outer ring</b>	Plastic
<b>Measurement force</b>	1 N
<b>Calibration Group</b>	CE
<b>Gross Weight</b>	0.301 kg
<b>Product Group</b>	331

### EAN

4039247207213