

Solid carbide quarter circle milling cutter

Concave

ORION[®]

Application:

Quarter circle milling cutter for machining complex forms, e.g. for very small radii on bores. With reduced diameter on the radius runoff so it can be used even in confined working conditions.



Execution:

- Straight shank pursuant to DIN 1636 HA
- Straight grooved
- K15 micro-fine grain

Art. no.	16711 800
Brand	ORION
Manufacturer Part Number	16711800
Cutting material	SC
Surface	Uncoated
Type	N
Number of cutting edges	2 PCS
Tool holding device	HA parallel shank
Radius	2 mm
Min. cutting edge diameter	1.5 mm
Max. cutting edge diameter	5.6 mm
Clearance length	8 mm
Length	50 mm
Clearance diameter	5.6 mm
Shank diameter	6 mm
fz steel 1000	0.022 mm
Gross Weight	0.021 kg
Product Group	150

EAN

4039247574049