

Solid carbide single tooth cutter

1 cutter, uncoated

ORION[®]

Application:

For milling, recessing and contour milling of non-ferrous metals and plastics.

Execution:

- solid carbide ultra-fine grain
- straight shank in accordance with DIN 6535 HA
- sharp-edged
- uncoated
- right-hand cutting

Delivery:

Up to 3 mm diameter = 10 pieces



Art. no.	16700 110
Brand	ORION
Manufacturer Part Number	16700110
Cutting material	SC
Surface	Uncoated
Type	W
Number of cutting edges	1 PCS
Twist angle	30°
Tool holding device	HA parallel shank
Construction length	Normal
Cutting edge diameter	1 mm
Cutting edge length	4 mm
Length	38 mm
Shank diameter	3 mm
fz aluminium	0.008 mm
Gross Weight	0.005 kg
Overall stainless steel suitability	3
fitness not iron total	1
fitness Titan/Nickel/Super total	3
Product Group	150

EAN

4039247573493