

## Pneumatic filing machine FRV 110

MANNESMANN  
DEMAG

### Application:

For (heavy-duty) file work in tool and mould making as well as deburring of cast and machine parts

### Execution:

- For files with round shaft
- Exhaust air towards the front
- Tool chuck, dia. 4 and 6 mm

### Advantage:

- Extremely low vibration levels: 2 m/s<sup>2</sup>
- Smooth running, high precision

### Delivery:

Without file accessories



<b>Art. no.</b>	<b>75061 470</b>
<b>Brand</b>	MANNESMANN DEMAG
<b>Manufacturer Part Number</b>	29701146
<b>Model</b>	FRV 110
<b>Valve design</b>	Lever valve
<b>Air consumption</b>	1.3 l/s
<b>Stroke rate</b>	9000 rpm
<b>Stroke length</b>	8 mm
<b>Weight</b>	1.05 kg
<b>Sound-pressure level</b>	77 dB
<b>Gross Weight</b>	1.030 kg
<b>Product Group</b>	7AA

### EAN

4251757300141