

SDXC steel boring bar, positive right

For longitudinal and copy turning with DC indexable insert

ATORN

Application:


For longitudinal and copy turning with DC 55° indexable insert.

Execution:

- precision-manufactured **steel** boring bar, with inner cooling, D type, 93° pitch angle, 55° tip angle, 7° clearance angle

Advantage:

- very slim geometry, optimised for contour turning work
- Positive body geometry ensures low cutting forces



Art. no.	17861 212
Brand	ATORN
Manufacturer Part Number	12232468
ISO name	A16Q SDXC R/L 07
Min. bore diameter	21 mm
Shank diameter	16 mm
Cutting edge height	4.3 mm
Clearance length	33 mm
Length	180 mm
Clamping surface height	15 mm
Suitable for indexable inserts	DC.. 07..
Tool design	Left
DIN	8024
Gross Weight	0.300 kg
Product Group	1AQ

EAN

4050293562101