

Wheeled workbenches with CLIP-O-FLEX hook-on system

Height 958 mm, including 12 CLIP-O-FLEX trays

CLIP-O-FLEX®

Application:

Thanks to the flexible and modular CLIP-O-FLEX system, the wheeled workbench can be optimally designed and adapted to the individual work sequences in production, assembly, development, training and further education. CLIP-O-FLEX sets your work/storage area or your organisation system with one clip and at the same time gives the highest level of horizontal and vertical flexibility.

Execution:

- Solidly welded steel sheet construction
- Workbench panel with CLIP-O-FLEX support rails installed on the left, right and at the rear
- With fixed support brackets on the inside for CLIP-O-FLEX trays

Advantage:

- Simply remove the trays from the cabinet and hang on the hook-in rails at the side
- Flexible hook-on system with only one hooking movement
- Ergonomic workplace design thanks to different inclines and can be relocated horizontally
- Quick access to work equipment, very clear overview
- Rapid conversion and replacement, highest possible level of mobility, less walking required, optimum use of space



Art. no.	50237 143
Brand	CLIP-O-FLEX
Manufacturer Part Number	28326
Number of drawers	2 PCS
Drawer front height	2 x 90 mm
Drawer width (inner dimension)	365 mm
Drawer depth (inner dimension)	294 mm
Load-carrying capacity per drawer	35 kg
Pullout type	Full extension
With single pull-out safety brake	No
Load-carrying capacity	550 kg
Dynamic load-carrying capacity	225 kg
Central locking	Yes
Lock type	Cylinder lock
With sliding handle	Yes
Number of fixed rollers	2 PCS
Number of steering rollers	2 PCS
With wheel lock	Yes
Material of wheel	Solid rubber
Wheel diameter	100 mm
Material of worktop	Multiplex beech
Material	Sheet steel
Cabinet colour	Optional
Colour of front	Optional
Surface	Powder-coated
Gross Weight	119.000 kg
Product Group	586