

## Drill/counter sink milling cutter, 90°, with Weldon shank

For AP... indexable milling inserts T604..

**ATORN**<sup>®</sup>

### Application


For drilling/countersinking in all materials.

### Version

- With Weldon shank
- Wear-resistant, nickel-plated version
- Robust supports
- Clamping screw tightening torque (indexable insert) M4 = 5.2 Nm

### Advantage

- High cutting performance
- Safe chip removal thanks to positive cutting geometry



<b>Art. No.</b>	<b>16019 010</b>
<b>Cutting edge diameter</b>	32 mm
<b>Clearance length</b>	50 mm
<b>Length</b>	130 mm
<b>Shaft diameter</b>	32 mm
<b>max. ap</b>	30 mm
<b>Number of cutting edges</b>	2 PCS
<b>Number of cutting inserts</b>	3 PCS
<b>Suitable indexable insert no.</b>	27

### EAN-Code

4050293113396

