

## AXIAL SILASTIC GUARD JUNCTION STANDARD RECTIFIER

## **BY251 THRU BY255**

VOLTAGE RANGE CURRENT 200 to 1300 Volts 3.0 Ampere


#### **FEATURES**

- Low coat construction
- Low forward voltage drop
- Low reverse leakage
- High forward surge current capability
- High temperature soldering guaranteed:

 $260\,^{\circ}\text{C}/10~\text{secods}/.375\text{"}(9.5\text{mm})\text{lead length at 5 lbs}(2.3\text{kg})~\text{tension}$ 

#### **MECHANICAL DATA**

- Case: Transfer molded plastic
- Epoxy: UL94V-O rate flame retardant
- Polarity: Color band denotes cathode end
- Lead: Plated axial lead, solderable per MIL-STD-202E method 208C
- Mounting position: Any
- Weight: 0.042 ounce, 1.19 grams



Dimensions in inches and (millimeters)

### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

- Ratings at 25°C ambient temperature unless otherwise specified
- Single Phase, half wave, 60Hz, resistive or inductive load
- For capacitive load derate current by 20%

		SYMBOLS	BY251	BY252	BY253	BY254	BY255	UNIT
Maximum Repetitive Peak Reverse Voltage		$V_{RRM}$	200	400	600	800	1300	Volts
Maximum RMS Voltage		$V_{RMS}$	140	280	420	560	910	Volts
Maximum DC Blocking Voltage		$V_{DC}$	200	400	600	800	1300	Volts
Maximum Average Forward Rectified Current 0.375"(9.5mm) lead length at $T_A$ = 75 $^{\circ}$ C		$I_{(AV)}$	3.0					Amps
Peak Forward Surge Current 8.3mS single half sine wave superimposed on rated load (JEDEC method)		$I_{FSM}$	125					Amps
Maximum Instantaneous Forward Voltage @ 3.0A		$V_F$	1.1					Volts
Maximum DC Reverse Current at Rated DC Blocking Voltage per element	$T_A = 25 ^{\circ}\text{C}$	$I_R$	5.0					μА
	$T_A = 100$ °C		50					
Maximum Full Load Reverse Current, full cycle average 0.375"(9.5mm)lead length at $T_L$ =75 $^{\circ}$ C		$I_{R(AV)}$	500					μА
Typical Junction Capacitance (Note 1)		$C_J$	40					pF
Typical Thermal Resistance (Note 2)		$R_{\theta JA}$	30					°C/W
Operating Junction Temperature Range		$T_{J}$	-55 to +150					°C
Storage Temperature Range		$T_{STG}$	-55 to +150					°C

#### Notes:

- 1. Measured at 1.0MHz and Applied Reverse Voltage of 4.0V DC.
- 2. Thermal Resistance from junction to ambient at .375"(9.5mm) lead length, P.C.board mounted.

Web Site: www.hkmic.com





## AXIAL SILASTIC GUARD JUNCTION STANDARD RECTIFIER


**BY251 THRU BY255** 

VOLTAGE RANGE CURRENT 200 to 1300 Volts 3.0 Ampere

# RATING AND CHRACTERISTIC CURVES BY251 Thur BY255











FIG.5-TYPICAL JUNCTION CAPACITANCE



Web Site: www.hkmic.com