

**EVO-STIK WEATHERPROOF WOOD ADHESIVE**  
Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

### 1.1. Product identifier

**Product Name** EVO-STIK WEATHERPROOF WOOD ADHESIVE  
**Pure substance/mixture** Mixture

### 1.2. Relevant identified uses of the substance or mixture and uses advised against

**Recommended use** Building and construction work.  
**Uses advised against** None known

### 1.3. Details of the supplier of the safety data sheet

#### Company Name

Bostik Limited  
Common Rd  
ST16 3EH  
Stafford UK  
Tel: +44 (1785) 27 26 25  
Fax: +44 (1785) 25 72 36

**E-mail address** SDS.box-EU@bostik.com

### 1.4. Emergency telephone number

**United Kingdom** +44 (1785) 272650  
**Ireland** +353 (1) 8624900 (Monday- Friday 9am-5pm)

## SECTION 2: Hazards identification

### 2.1. Classification of the substance or mixture

Regulation (EC) No 1272/2008

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

### 2.2. Label elements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

#### Signal word

None

#### Hazard statements

This mixture is classified as not hazardous according to regulation (EC) 1272/2008 [CLP]

#### EU Specific Hazard Statements

EUH208 - Contains reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT]. May produce an allergic reaction

#### Precautionary Statements - EU (§28, 1272/2008)

P101 - If medical advice is needed, have product container or label at hand  
P102 - Keep out of reach of children

### 2.3. Other hazards

No information available.

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

## PBT & vPvB

This mixture contains no substance considered to be persistent, bioaccumulating or toxic (PBT). This mixture contains no substance considered to be very persistent nor very bioaccumulating (vPvB).

## SECTION 3: Composition/information on ingredients

### 3.1 Substances

Not applicable

### 3.2 Mixtures

Chemical name	EC No	CAS No	Weight-%	Classification according to Regulation (EC) No. 1272/2008 [CLP]	Specific concentration limit (SCL)	REACH registration number
Propylene carbonate	203-572-1	108-32-7	1 - <5	Eye Irrit. 2 (H319)		01-2119537232-48-XXXX
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT]	611-341-5	55965-84-9	<0.0015	Acute Tox. 3 (H301) Acute Tox. 2 (H310) Acute Tox. 2 (H330) Skin Corr. 1C (H314) Eye Dam. 1 (H318) Skin Sens. 1A (H317) Aquatic Acute 1 (H400) Aquatic Chronic 1 (H410) M Factor Acute = 100 M Factor Chronic = 100	Eye Dam. 1 :: C>=0.6% Irrit. 2 :: 0.06%<=C<0.6% Skin Corr. 1C :: C>=0.6% Skin Irrit. 2 :: 0.06%<=C<0.6% Skin Sens. 1 :: C>=0.0015%	01-2120764691-48-XXXX

Full text of H- and EUH-phrases: see section 16

This product does not contain candidate substances of very high concern at a concentration  $\geq 0.1\%$  (Regulation (EC) No. 1907/2006 (REACH), Article 59)

## SECTION 4: First aid measures

### 4.1. Description of first aid measures

<b>General advice</b>	Show this safety data sheet to the doctor in attendance.
<b>Inhalation</b>	Remove to fresh air. IF exposed or concerned: Get medical advice/attention.
<b>Eye contact</b>	Rinse thoroughly with plenty of water for at least 15 minutes, lifting lower and upper eyelids. Consult a doctor.
<b>Skin contact</b>	Wash skin with soap and water. In the case of skin irritation or allergic reactions see a

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
Supercedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

doctor.

**Ingestion** Clean mouth with water. Do NOT induce vomiting. Drink 1 or 2 glasses of water. Never give anything by mouth to an unconscious person.

#### 4.2. Most important symptoms and effects, both acute and delayed

**Symptoms** No information available.

#### 4.3. Indication of any immediate medical attention and special treatment needed

**Note to doctors** Treat symptomatically.

### **SECTION 5: Firefighting measures**

#### 5.1. Extinguishing media

**Suitable Extinguishing Media** Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

**Unsuitable extinguishing media** No information available.

#### 5.2. Special hazards arising from the substance or mixture

**Specific hazards arising from the chemical** No information available.

**Hazardous combustion products** Carbon dioxide (CO<sub>2</sub>).

#### 5.3. Advice for firefighters

**Special protective equipment and precautions for fire-fighters** Firefighters should wear self-contained breathing apparatus and full firefighting turnout gear. Use personal protection equipment.

### **SECTION 6: Accidental release measures**

#### 6.1. Personal precautions, protective equipment and emergency procedures

**Personal precautions** Ensure adequate ventilation.

**For emergency responders** Use personal protection recommended in Section 8.

#### 6.2. Environmental precautions

**Environmental precautions** See Section 12 for additional Ecological Information.

#### 6.3. Methods and material for containment and cleaning up

**Methods for containment** Prevent further leakage or spillage if safe to do so.

**Methods for cleaning up** Take up mechanically, placing in appropriate containers for disposal.

**Prevention of secondary hazards** Clean contaminated objects and areas thoroughly observing environmental regulations.

#### 6.4. Reference to other sections

**Reference to other sections** See section 8 for more information. See section 13 for more information.

### **SECTION 7: Handling and storage**

#### 7.1. Precautions for safe handling

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
 Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
 Revision Number 1.04

**Advice on safe handling** Ensure adequate ventilation.  
**General hygiene considerations** Handle in accordance with good industrial hygiene and safety practice.

## 7.2. Conditions for safe storage, including any incompatibilities

**Storage Conditions** Keep container tightly closed in a dry and well-ventilated place.

## 7.3. Specific end use(s)

**Specific use(s)**  
 Building and construction work.

**Risk Management Methods (RMM)** The information required is contained in this Safety Data Sheet.

**Other information** Observe technical data sheet.

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Exposure Limits

**Derived No Effect Level (DNEL)** No information available

Derived No Effect Level (DNEL)			
Propylene carbonate (108-32-7)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
worker Long term Systemic health effects	Inhalation	70.53 mg/m <sup>3</sup>	
worker Long term Local health effects	Inhalation	20 mg/m <sup>3</sup>	
worker Long term Systemic health effects	Dermal	20 mg/kg bw/d	
worker Long term Local health effects	Dermal	10 mg/cm <sup>2</sup>	

Derived No Effect Level (DNEL)			
Propylene carbonate (108-32-7)			
Type	Exposure route	Derived No Effect Level (DNEL)	Safety factor
Consumer Long term Systemic health effects	Inhalation	17.4 mg/m <sup>3</sup>	
Consumer Long term Local health effects	Inhalation	10 mg/m <sup>3</sup>	
Consumer Long term Systemic health effects	Dermal	10 mg/kg bw/d	
Consumer Long term Systemic health effects	Oral	10 mg/kg bw/d	

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

**Predicted No Effect Concentration (PNEC)** No information available.

Predicted No Effect Concentration (PNEC)	
Propylene carbonate (108-32-7)	
Environmental compartment	Predicted No Effect Concentration (PNEC)
Freshwater	0.9 mg/l
Marine water	0.09 mg/l
Soil	0.81 mg/kg dry weight
Sewage treatment plant	7400 mg/l

## 8.2. Exposure controls

**Engineering controls** Ensure adequate ventilation, especially in confined areas.

### Personal protective equipment

#### Eye/face protection

Wear safety glasses with side shields (or goggles). Eye protection must conform to standard EN 166.

#### Hand protection

Wear suitable gloves. Gloves must conform to standard EN 374. Recommended Use: Polyvinyl chloride (PVC). The breakthrough time for the mentioned glove material is in general greater than 480 min. Ensure that the breakthrough time of the glove material is not exceeded. Refer to glove supplier for information on breakthrough time for specific gloves.

#### Skin and body protection

Wear suitable protective clothing. Material, acid-resistant.

#### Respiratory protection

No protective equipment is needed under normal use conditions. If exposure limits are exceeded or irritation is experienced, ventilation and evacuation may be required.

**Environmental exposure controls** Do not allow uncontrolled discharge of product into the environment.

## SECTION 9: Physical and chemical properties

### 9.1. Information on basic physical and chemical properties

Physical state	Liquid
Appearance	Liquid
Colour	White
Odour	Sweet
Odour threshold	No information available

Property	Values	Remarks • Method
pH	2.8 - 3.6	
pH (as aqueous solution)	No data available	
Melting point / freezing point	No data available	
Initial boiling point and boiling range	100 °C	
Flash point	No data available	
Evaporation rate	No data available	
Flammability	Not applicable for liquids	
Flammability Limit in Air		
Upper flammability or explosive limits	No data available	
Lower flammability or explosive limits	No data available	
Vapour pressure	24	hPa
Relative vapour density	No data available	
Relative density	No data available	
Water solubility	Miscible in water	
Solubility(ies)	No data available	
Partition coefficient	No data available	
Autoignition temperature	No data available	
Decomposition temperature	No data available	
Kinematic viscosity	No data available	

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE

Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021

Revision Number 1.04

---

Dynamic viscosity	9000 - 15000 mPa s
Explosive properties	No data available
Oxidising properties	No data available

## 9.2. Other information

Solid content (%)	No information available
VOC Content (%)	
Density	1.03 - 1.13 g/ml

## **SECTION 10: Stability and reactivity**

### 10.1. Reactivity

Reactivity No information available.

### 10.2. Chemical stability

Stability Stable under normal conditions.

### Explosion data

Sensitivity to mechanical impact None.

Sensitivity to static discharge None.

### 10.3. Possibility of hazardous reactions

Possibility of hazardous reactions None under normal processing.

### 10.4. Conditions to avoid

Conditions to avoid None known based on information supplied.

### 10.5. Incompatible materials

Incompatible materials None known based on information supplied.

### 10.6. Hazardous decomposition products

Hazardous decomposition products Carbon monoxide. Carbon dioxide (CO<sub>2</sub>). Hydrocarbons.

## **SECTION 11: Toxicological information**

### 11.1. Information on toxicological effects

#### Information on likely routes of exposure

#### Product Information

Inhalation Based on available data, the classification criteria are not met.

Eye contact Based on available data, the classification criteria are not met.

Skin contact Based on available data, the classification criteria are not met.

Ingestion Based on available data, the classification criteria are not met.

#### Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

## Numerical measures of toxicity

### Acute toxicity

### Component Information

Chemical name	Oral LD50	Dermal LD50	Inhalation LC50
Propylene carbonate 108-32-7	LD50 > 5000 mg/kg (Rattus) OECD 401	> 3000 mg/kg (Oryctolagus cuniculus)	
reaction mass of 5-chloro-2-methyl-2H-isothiazolo l-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT] 55965-84-9	=53 mg/kg (Rattus)	LD50 = 87.12 mg/kg (Oryctolagus cuniculus)	

## Delayed and immediate effects as well as chronic effects from short and long-term exposure

**Skin corrosion/irritation** Based on available data, the classification criteria are not met.

**Serious eye damage/eye irritation** Based on available data, the classification criteria are not met.

**Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.

**Germ cell mutagenicity** Based on available data, the classification criteria are not met.

**Carcinogenicity** Based on available data, the classification criteria are not met.

**Reproductive toxicity** Based on available data, the classification criteria are not met.

**STOT - single exposure** Based on available data, the classification criteria are not met.

**STOT - repeated exposure** Based on available data, the classification criteria are not met.

**Aspiration hazard** Based on available data, the classification criteria are not met.

## 11.2. Information on other hazards

### 11.2.1. Endocrine disrupting properties

**Endocrine disrupting properties** No information available.

### 11.2.2. Other information

**Other adverse effects** No information available.

## **SECTION 12: Ecological information**

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

## 12.1. Toxicity

### Ecotoxicity

Chemical name	Algae/aquatic plants	Fish	Toxicity to microorganisms	Crustacea	M-Factor	M-Factor (long-term)
Propylene carbonate 108-32-7	EC50: >500mg/L (72h, Desmodesmus subspicatus)	LC50 96 h > 1000 mg/L (Cyprinus carpio semi-static)	EC50 > 10000 mg/L 17 h	EC50: >500mg/L (48h, Daphnia magna)		
reaction mass of 5-chloro-2-methyl-2H-is othiazol-3-one and 2-methyl-2H-isothiazol- 3-one (3:1) [C(M)IT/MIT] 55965-84-9	EC50 (72h) =0.048 mg/L (Pseudokirchner iella subcapitata) (OECD 201)	EC50 (96h) = 0.22 mg/L (Oncorhynchus mykiss) (OECD 211)	-	EC50 (48h) =0.1 mg/L (Daphnia magna) (OECD 202)	100	100

## 12.2. Persistence and degradability

**Persistence and degradability** No information available.

## 12.3. Bioaccumulative potential

**Bioaccumulation** There is no data for this product.

## Component Information

Chemical name	Partition coefficient	Bioconcentration factor (BCF)
Propylene carbonate 108-32-7	0.079	-
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT] 55965-84-9	-	3.16

## 12.4. Mobility in soil

**Mobility in soil** No information available.

## 12.5. Results of PBT and vPvB assessment

**PBT and vPvB assessment** . The product does not contain any substance(s) classified as PBT or vPvB.

Chemical name	PBT and vPvB assessment
Propylene carbonate 108-32-7	The substance is not PBT / vPvB
reaction mass of 5-chloro-2-methyl-2H-isothiazol-3-one and 2-methyl-2H-isothiazol-3-one (3:1) [C(M)IT/MIT] 55965-84-9	The substance is not PBT / vPvB

## 12.6. Other adverse effects

**Other adverse effects** No information available.

## SECTION 13: Disposal considerations



# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE  
Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021  
Revision Number 1.04

## 13.1. Waste treatment methods

<b>Waste from residues/unused products</b>	Dispose of in accordance with local regulations. Dispose of waste in accordance with environmental legislation.
<b>Contaminated packaging</b>	Do not reuse empty containers.
<b>Other information</b>	Waste codes should be assigned by the user based on the application for which the product was used.

## **SECTION 14: Transport information**

### Land transport (ADR/RID)

<b>14.1 UN number or ID number</b>	Not regulated
<b>14.2 Proper Shipping Name</b>	Not regulated
<b>14.3 Transport hazard class(es)</b>	Not regulated
<b>14.4 Packing group</b>	Not regulated
<b>14.5 Environmental hazards</b>	Not applicable
<b>14.6 Special Provisions</b>	None

### IMDG

<b>14.1 UN number or ID number</b>	Not regulated
<b>14.2 Proper Shipping Name</b>	Not regulated
<b>14.3 Transport hazard class(es)</b>	Not regulated
<b>14.4 Packing group</b>	Not regulated
<b>14.5 Marine pollutant</b>	NP
<b>14.6 Special Provisions</b>	None
<b>14.7 Transport in bulk according to Annex II of MARPOL and the IBC Code</b>	Not applicable

### Air transport (ICAO-TI / IATA-DGR)

<b>14.1 UN number or ID number</b>	Not regulated
<b>14.2 Proper Shipping Name</b>	Not regulated
<b>14.3 Transport hazard class(es)</b>	Not regulated
<b>14.4 Packing group</b>	Not regulated
<b>14.5 Environmental hazards</b>	Not applicable
<b>14.6 Special Provisions</b>	None

## **Section 15: REGULATORY INFORMATION**

### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

#### European Union

Take note of Directive 98/24/EC on the protection of the health and safety of workers from the risks related to chemical agents at work

Check whether measures in accordance with Directive 94/33/EC for the protection of young people at work must be taken.

Take note of Directive 92/85/EC on the protection of pregnant and breastfeeding women at work

#### Registration, Evaluation, Authorization, and Restriction of Chemicals (REACH) Regulation (EC 1907/2006)

##### **SVHC: Substances of Very High Concern for Authorisation:**

This product does not contain candidate substances of very high concern at a concentration  $\geq 0.1\%$  (Regulation (EC) No. 1907/2006 (REACH), Article 59)

# SAFETY DATA SHEET

EVO-STIK WEATHERPROOF WOOD ADHESIVE

Supersedes Date: 19-Nov-2020

Revision date 22-Mar-2021

Revision Number 1.04

## EU-REACH (1907/2006) - Annex XVII - Substances subject to Restriction

This product does not contain substances subject to restriction (Regulation (EC) No. 1907/2006 (REACH), Annex XVII).

## Substance subject to authorisation per REACH Annex XIV

This product does not contain substances subject to authorisation (Regulation (EC) No. 1907/2006 (REACH), Annex XIV)

## Biocidal Products Regulation (EU) No 528/2012 (BPR)

Contains a biocide : Contains C(M)IT/MIT (3:1). May produce an allergic reaction

## Ozone-depleting substances (ODS) regulation (EC) 1005/2009

Not applicable

## Persistent Organic Pollutants

Not applicable

## National regulations

### 15.2. Chemical safety assessment

Chemical Safety Assessments have been carried out by the Reach registrants for substances registered at >10 tpa. No Chemical Safety Assessment has been carried out for this mixture

## SECTION 16: Other information

### Key or legend to abbreviations and acronyms used in the safety data sheet

#### Full text of H-Statements referred to under section 3

H301 - Toxic if swallowed  
H310 - Fatal in contact with skin  
H314 - Causes severe skin burns and eye damage  
H317 - May cause an allergic skin reaction  
H318 - Causes serious eye damage  
H319 - Causes serious eye irritation  
H330 - Fatal if inhaled  
H400 - Very toxic to aquatic life  
H410 - Very toxic to aquatic life with long lasting effects

#### Legend

TWA	TWA (time-weighted average)
STEL	STEL (Short Term Exposure Limit)
Ceiling	Ceiling Limit Value
*	Skin designation
SVHC	Substance(s) of Very High Concern
PBT	Persistent, Bioaccumulative, and Toxic (PBT) Chemicals
vPvB	Very Persistent and very Bioaccumulative (vPvB) Chemicals
STOT RE	Specific target organ toxicity - Repeated exposure
STOT SE	Specific target organ toxicity - Single exposure
EWC	European Waste Catalogue

#### Key literature references and sources for data

No information available

Prepared By

Product Safety & Regulatory Affairs

# SAFETY DATA SHEET

**EVO-STIK WEATHERPROOF WOOD ADHESIVE**  
**Supersedes Date:** 19-Nov-2020

**Revision date** 22-Mar-2021  
**Revision Number** 1.04

---

**Revision date** 22-Mar-2021

**Indication of changes**

**Revision note** Not applicable.

**Training Advice** No information available

**Further information** No information available

**This material safety data sheet complies with the requirements of Regulation (EC) No. 1907/2006**

## **Disclaimer**

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text.

**End of Safety Data Sheet**