

## Conical drill bit HSS TiN

For universal use up to 1300 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:


For producing bores in thin sheets made from steel, non-ferrous metals and cast iron. Also suitable for all plastics, for hard paper and plywood, as well as all materials of similar structure and strength

### Execution:

- Profile-ground to meet the highest requirements for dimensional accuracy and process reliability

### Advantage:

- Innovative cutting geometry: All bores are burr and chatter free
- User-friendly regrinding: Drills can be reground repeatedly
- No deformations even with the thinnest material thicknesses



<b>Art. no.</b>	<b>11401 020</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11401020
<b>Cutting material</b>	HSS
<b>Surface</b>	TiN
<b>Tool holding device</b>	Cylinder shank
<b>Type</b>	2
<b>Min./max. cutting edge diameter</b>	16-30.5 mm
<b>Shank diameter</b>	9 mm
<b>Length</b>	71 mm
<b>DIN</b>	344
<b>Gross Weight</b>	0.200 kg
<b>Product Group</b>	103

### EAN

4039247035229