

RECORD ARKANSAS gouge stones

Type 9010 A 4

LAPPORT
SCHLEIFTECHNIK

Application:

For sharpening all kinds of tools and for machining hard or abrasive materials such as quartz, glass or ceramics, with two round edges of different strengths.

Execution:

- For use with oil or petroleum
- Synthetic honing stones, manufactured according to a special ceramic process

Delivery:

In cardboard box



Art. no.	69432 010
Brand	LAPPORT
Manufacturer Part Number	100297
Length	115 mm
Surface structure	Very fine
Number of pieces per packet	6 PCS
Binding	Ceramically bound
Width	45 mm
Thickness	6/2 mm
Form	Round
Suitable for finishing	1 - very suitable
Suitable for main machining	3 - less suitable
Suitable for surface inspection	1 - very suitable
Suitable for surface care	1 - very suitable
Suitable for material rubber	3 - less suitable
Suitable for material cast iron	3 - less suitable
Suitable for material HSS	1 - very suitable
Suitable for material carbide	3 - less suitable
Suitable for material ceramic	3 - less suitable
Suitable for material plastics	3 - less suitable
Suitable for material non-ferrous metals	3 - less suitable
Suitable for material steel (hardened)	1 - very suitable
Suitable for material steel (unhardened)	2 - suitable
Suitable for material tool steel	2 - suitable
ISO	525
Length x width	115 x 45 mm
Length x width x thickness	115 x 45 x 6/2 mm
Type description	RECORD-ARKANSAS
Material of abrasive medium	Fused aluminium oxide
Gross Weight	0.057 kg
Product Group	6HL