

Dial gauges IP67

with shock protection

Application:

For measuring lengths and differences in length, e.g. concentricity, flatness, position measurements.

Execution:

- Measuring pin and clamping shank are made from durable stainless steel
- With screwed-on metal ring for maximum impermeability
- Protection class IP67

Delivery:

in case



Art. no.	33052 010
Brand	HK
Manufacturer Part Number	33052010
Length measuring range	10 mm
Scale value	0.01 mm
Measurement travel of one pointer revolution	1 mm
Outer diameter	61 mm
Shock protection	Yes
Material of outer ring	Metal
IP protection class	IP 67
Measurement force	1.2 N
DIN	878
Calibration Group	CE
Gross Weight	0.275 kg
Product Group	331

EAN

4039247393114