

Solid carbide HSC single-tooth milling cutter – left-hand spiral

1 cutter, uncoated

ATORN®



Application

For the milling, grooving and contour milling of standard plastics.

Version

- Solid carbide ultra-fine grain
- Straight shank in line with DIN 6535 HA
- Uncoated
- Surface polished
- With centre cutting
- For soft standard plastics like thermoplastics PVC, PE, PP, etc.
- DownCut

Advantage

- Ideal for sheet metal, boards and thin-walled materials
- Large chip space for easy chip removal

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plas- tics	Graphite G(C)FK	GG(G) GjMW	Titan- alloy	Nickel- alloy	Super- alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
												345							

Art. No.	16656 420
Cutting material	VHM
Surface	Uncoated
Type	Left-hand twist
Number of cutting edges	1 PCS
Twist angle	30°
Tool holding device	HA parallel shank
Overall length	Normal
Cutting edge diameter	3 mm
Cutting edge length	12 mm
Length	64 mm
Shaft diameter	6 mm
fz aluminium	0.15 mm
Overall stainless steel suitability	3
fitness not iron total	3
fitness Titan/Nickel/Super total	3

EAN-Code

4050293435108