



NOTE:

1. Electrical test:

- (1). 100% open short & miss wire test
- (2). Insulation resistance: DC 100V 0.01S 5M ohm
- (3). Contactor resistance: 3 ohm Max

2. Feature:

Full-featured USB4 Type-C Cable (USB4 Gen2x2)
 Transmission rate Up to 20Gbps
 Resolution 3840*2160@60Hz
 Backwards compatible with USB 3.1, 3.0 and 2.0 and Thunderbolt 3
 Supports USB power delivery 3.0 (EPR 5-20V 5A)100W

3. RoHS and REACH Compliant

MATERIAL LIST:

| ⑤ | OUT MOLD | TPE Moulding | 2 | |
|-----|------------|--|-------|--------|
| ④ | INNER MOLD | LD-PE | 2 | |
| ③ | E-mark | USB4 GEN2*2 20Gbps 100W/5A Max | 1 | |
| ② | TYPE C | USB4 C/M SOLDER TYPE, BLACK PBT INSULATION, THE PIN GOLD PLATING, THE SHELL FOR NICKEL PLATING+IRON SHIELD | 2 | |
| ① | CABLE | USB4 GEN2*2 CABLE [1P*30AWG+D+AL+HM]*4C+1P*32AWG+4C*32AWG+2C*23AWG+F+D+AB TPE JACKET BLACK OD: 4.8±0.15MM | 1 | |
| NO. | PARTS NAME | SPECIFICATION STANDARD | QT' Y | REMARK |

| | |
|-----------------|---|
| Desc. | ROLINE USB4 Gen 2x2 (20G.bits) Cable, CM-CM, 100W, black, 2m |
| Item No. | 11.02.9083 |

SECOMP

| | | | | |
|----|-----|-------------------------------|------------|------|
| | | | 2022-06-23 | A |
| BY | CHK | REVISION RECORD MODIFICATIONS | DATE | REV. |