

3-point internal micrometer set

IMICRO



Application:

For high-precision measurement of through-bores, even at high measuring depths.

Execution:

- Carbide measuring faces
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning

Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

Delivery:

Individual devices, setting rings, measuring depth extensions from 6 mm to 12 mm, in a case



Art. no.	31688 100
Brand	TESA
Manufacturer Part Number	00813409
Min./max. length measuring range	3.5-6.5 mm
Measuring depth	20/25 mm
Error limit	4 µm
Digit increment	0.001 mm
Adjusting ring diameter	5,5 mm, 4 mm
DIN	863
Calibration Group	I
Gross Weight	0.500 kg
Product Group	362

EAN

7630041108323