



SCALANCE XP208POE EEC, MANAGED IE SWITCH, 8 X 10/100MBIT/S M12-PORTS, IP65/67, LED-DIAGNOSIS, FAULT SIGNAL CONTACT, REDUNDAND POWER SUPPLY, PROFINET IO DEVICE, NETWORK MANAGEMENT, OPERATION IN RED. RING, INCL. DUST COVERS, INCL. ELECTRON. MANUAL ON CD, C-PLUG OPTIONAL

Transmission rate	
Transfer rate	10 Mbit/s, 100 Mbit/s
Interfaces / for communication / integrated	
Number of electrical connections	
• for network components or terminal equipment	8
Number of 10/100 Mbit/s M12-ports (D-coded) / Integrated	4
• with PoE	4
Interfaces / others	
Number of electrical connections	
• for operator console	1
• for signaling contact	1
• for power supply	1
• for redundant voltage supply	1
Type of electrical connection	
• for operator console	5 pin M12 socket (A coded)
design of the removable storage	
• C-PLUG	Yes

Signal-Inputs/outputs

Operating voltage / of the signaling contacts	
• at DC / Rated value	54 V
Operating current / of the signaling contacts	
• at DC / maximum	0.1 A

Supply voltage, current consumption, power loss

Type of voltage / of the supply voltage	DC
Supply voltage	
• external	54 V
• external / minimum	46 V
• external / maximum	57 V
Supply voltage / 1 / Rated value	
• Consumed current / 1 / at rated supply voltage / maximum	2.5 A
• Power loss [W] / 1 / Rated value	9 W
Product component / fusing at power supply input	Yes
Consumed current / maximum	2.4 A
Power loss [W]	
• maximum	9 W
Supplied active power / of PSE / with PoE	
• per port / maximum	120 W

Permitted ambient conditions

Ambient temperature	
• during operation	-40 ... +70 °C
• during storage	-40 ... +70 °C
• during transport	-40 ... +70 °C
Relative humidity	
• at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP65

Design, dimensions and weight

Design	compact
Width	200 mm
Height	200 mm
Depth	49 mm
Net weight	1.8 kg
Product feature / conformal coating	Yes
Material / of the enclosure	Aluminum
Mounting type	ET200pro module carrier
• wall mounting	Yes

Product properties, functions, components / general

Cascading in the case of a redundant ring / at reconfiguration time of $\leq 0.3\text{ s}$	50
Cascading in cases of star topology	any (depending only on signal propagation time)

Product functions / management, configuration

Product function	
• CLI	Yes
• web-based management	Yes
• MIB support	Yes
• TRAPs via email	Yes
• Configuration with STEP 7	Yes
• RMON	Yes
• Port mirroring	Yes
• multiport mirroring	Yes
• CoS	Yes
• with IRT / PROFINET IO switch	No
• PROFINET IO diagnosis	Yes
• switch-managed	Yes
Telegram length / for Ethernet / maximum	1518 byte
Protocol / is supported	
• Telnet	Yes
• HTTP	Yes
• HTTPS	Yes
• TFTP	Yes
• FTP	Yes
• BOOTP	No
• DCP	Yes
• LLDP	Yes
• EtherNet/IP	Yes
• SNMP v1	Yes
• SNMP v2	Yes
• SNMP v3	Yes
• IGMP (snooping/querier)	Yes
Identification & maintenance function	
• I&M0 - device-specific information	Yes
• I&M1 – higher-level designation/location designation	Yes

Product functions / Diagnosis

Product function	
• Port diagnostics	Yes
• Statistics Packet Size	Yes
• Statistics packet type	Yes

• Error statistics	Yes
• SysLog	Yes
• loopback diagnostics	Yes

Product functions / VLAN

Product function	
• VLAN - port based	Yes
• VLAN - protocol-based	No
• VLAN - IP-based	No
• VLAN dynamic	No
Number of VLANs / maximum	4094

Product functions / DHCP

Product function	
• DHCP server	Yes
• DHCP client	Yes
• DHCP Option 82	Yes
• DHCP Option 66	Yes
• DHCP Option 67	Yes

Product functions / Redundancy

Product function	
• Ring redundancy	Yes
• High Speed Redundancy Protocol (HRP)	Yes
• high speed redundancy protocol (HRP) with redundancy manager	Yes
• high speed redundancy protocol (HRP) with standby redundancy	Yes
Protocol / is supported / Media Redundancy Protocol (MRP)	Yes
Product function	
• media redundancy protocol (MRP) with redundancy manager	Yes
• redundancy procedure RSTP	Yes
• redundancy procedure MSTP	Yes
• Passive listening	Yes

Product functions / Security

Product function	
• RADIUS client	Yes
Protocol / is supported	
• SSH	Yes
• SSL	Yes

Product functions / Time

Product function	
<ul style="list-style-type: none"> • SICLOCK support • NTP-client • SNTP client 	<p>Yes</p> <p>Yes</p> <p>Yes</p>
Protocol / is supported	
<ul style="list-style-type: none"> • NTP • SNTP 	<p>Yes</p> <p>Yes</p>

Standards, specifications, approvals

Standard	
<ul style="list-style-type: none"> • for FM • for hazardous zone • for safety / from CSA and UL • for hazardous zone / from CSA and UL • for emitted interference • for interference immunity 	<p>FM3611: Class 1, Divison 2, Group A, B, C, D / T4, CL.1, Zone 2, GP. IIC, T4</p> <p>EN 60079-0 : 2006, EN 60079-15: 2005, II 3 G Ex nA II T4 KEMA 07 ATEX 0145X</p> <p>UL 60950-1, CSA C22.2 No. 60950-1</p> <p>ANSI / ISA 12.12.01, CSA C22.2 No. 213-M1987, CL. 1 / Div. 2 / GP. A, B, C, D T4, CL. 1 / Zone 2 / GP. IIC, T4</p> <p>EN 61000-6-4 (Class A)</p> <p>EN 61000-6-2</p>

Standards, specifications, approvals / CE

Certificate of suitability / CE marking	Yes
Certificate of suitability / RoHS conformity	Yes

Standards, specifications, approvals / miscellaneous

Certificate of suitability	
<ul style="list-style-type: none"> • C-Tick • E1 approval • e1 approval • Railway application in accordance with EN 50155 • Railway application in accordance with EN 50124-1 • Fire protection in accordance with EN 45545-2 • KC approval 	<p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p> <p>Yes</p>

Standards, specifications, approvals / product conformity

MTBF / at 40 °C	55 y
-----------------	------

Accessories

Product extension / optional / C-PLUG	Yes
---------------------------------------	-----

Further Information / Internet Links

Internet-Link	
<ul style="list-style-type: none"> • to website: Selector SIMATIC NET SELECTION TOOL • to website: Industrial communication 	<p>http://www.siemens.com/snst</p> <p>http://www.siemens.com/simatic-net</p>

- to website: Industry Mall
- to website: Information and Download Center
- to website: Image database
- to website: CAx Download Manager
- to website: Industry Online Support

<https://mall.industry.siemens.com>

<http://www.siemens.com/industry/infocenter>

<http://automation.siemens.com/bilddb>

<http://www.siemens.com/cax>

<https://support.industry.siemens.com>

last modified:

09/20/2017