

Cabinet trolley with 5 loading areas – with total stop

Grating on 3 sides and doors, total carrying capacity of 750 kg

fetra
Transportgeräte

Application:

For the safe transport and storage of materials and goods.

Execution:

- Angular steel structure completely welded with tubular push handle
- Front walls, 1 longitudinal wall and roof made from wire grid (40 x 40 x 4 mm)
- With double winged door made of angular steel with welded in wire grid
- Double winged door with vertical locking rod with swivelling lever and cylinder lock
- 1 fixed and 4 loose bases
- Made of rigid sandwich plates
- Clear floor distance 280 mm
- 2 fixed castors and 2 swivel castors, including TOTALSTOP
- With shootbolt rod

Advantage:

- Convenient total stop included

Delivery:

Assembled



Art. no.	50258 782
Brand	FETRA
Manufacturer Part Number	5392/7016
Material of loading surface	Wood
Load-carrying capacity	750 kg
Load-carrying capacity of loading surfaces	90 kg
Number of loading surfaces	5 PCS
Loading surface size	1000 x 680 mm
Loading-surface width	680 mm
Loading-surface height	292 mm, 582 mm, 882 mm, 1182 mm, 1482 mm
Loading surface length	1000 mm
Length	1170 mm
Width	745 mm
Height	1792 mm
Number of panels	4 PCS
Material of wall	Wire mesh
Number of fixed rollers	2 PCS
Length x width x height	1170 x 745 x 1792 mm
Number of steering rollers	2 PCS
With wheel lock	Totalstop
Wheel width	40 mm
Wheel diameter	200 mm
Material of wheel	TPE
Lock type	Cylinder lock
Colour	Anthracite grey RAL 7016
Surface	Powder-coated
Colour of loading area	Medium grey
Gross Weight	144.000 kg
Product Group	5AE

EAN

4017976253923