

SCRAPERS, PIN VICES, CHUCKS & COLLETS



Hand scrapers are designed for the removal of high spots on machined surfaces to give a smoother surface on slideways, bearings, cast iron surface plates and precision marking out plates. All scrapers have a soft feel handle and are made from high grade tool steel suitably hardened, to maintain a very keen cutting edge

Engineers' Scrapers

Suitable for toolroom and small engineering work

Part No	Blade Length	Cutting Edge	Pack Size
1 96A	100mm (4")	Three Square	5
2 97A	140mm (5½")	Three Square	5
99A	200mm (8")	Three Square	5
3 96B	100mm (4")	Flat	5
4 97B	150mm (6")	Flat	5
99B	200mm (8")	Flat	5
5 96C	100mm (4")	Curved half round	5
97C	150mm (6")	Curved half round	5
97D	200mm (8")	Curved half round	5
96	Set of 3 comprising Nos 96A, B, and C	1 set	
97	Set of 4 comprising Nos 97A, B, C and D	1 set	

Erector Scrapers

Suitable for large jobs or heavy engineering. Manufactured from chrome vanadium steel

Part No	Overall Length	Blade Length	Cutting Edge	Pack Size
256	335mm (13¼")	210mm (8¼")	Flat	5
6 257	350mm (14")	225mm (9")	Curved	5

Pin Vices

Hand held tools designed for holding round materials. Hollow handle enables material greater than the overall length of the pin chuck to be used

Part No	Capacity	Type	mm	inches	Overall Length	Pack Size
121	Chuck	0-1.0	0-0.04	75mm (3")	10	
122	Chuck	0.75-1.5	0.03-0.062	85mm (3½")	10	
123	Chuck	1.4-3.1	0.055-0.122	95mm (3¾")	10	
124	Chuck	3.1-5.00	0.122-0.196	105mm (4¼")	10	
8 120	Set of 1 each (121, 122, 123 and 124)				1 set	

Pin Chuck & Replacement Collects

Used for gripping very small drills, mainly on automatic lathes, where pin chuck does not revolve

Part No	Overall Length mm/inches	Description	Pack Size
9 160	65mm (2½")	Chuck with 3 collets capacity from 0.25-2.5mm(0.01-0.1")	1
RP621HRD		Replacement Collet capacity from 0.25-0.75mm(0.01-0.03")	1
RP622MRD		Replacement Collet capacity from 0.75-1.5mm(0.03-0.06")	1
RP623FRD		Replacement Collet capacity from 1.5-2.5mm(0.06-0.10")	1

Bearing Scrapers

Part No	Overall Length	Blade Length	Pack Size
2584	180mm (7¼")	100mm (4")	5
2586	240mm (9½")	150mm (6")	5
7 2588	290mm (11½")	200mm (8")	5
258	Set of 3 comprising 258/4, 258/6 and 258/8		1 set

NUTSPINNERS

Nut Spinner - BA

Part No	Blade Length	Blade Size	Pack Size
7800	150mm (6")	0 BA	6
7801	150mm (6")	1 BA	6
7802	150mm (6")	2 BA	6
7803	150mm (6")	3 BA	6
7804	150mm (6")	4 BA	6
7806	150mm (6")	6 BA	6



For loosening and securing nuts particularly where spanners cannot reach or are awkward to use. Tribolular handle with tapered neck for ergonomic fit. Dual material handle for comfort in use. Integral moulded finger grips around neck to allow increased torque

Nut Spinner - Metric

Part No	Blade Length	Blade Size	Pack Size
7840	150mm (6")	4mm	6
7850	150mm (6")	5mm	6
7855	150mm (6")	5.5mm	6
7860	150mm (6")	6mm	6
7870	150mm (6")	7mm	6
7880	150mm (6")	8mm	6
7810	150mm (6")	10mm	6
7830*	7mm (½") AF, flexible shaft, with thicker handle for improved working grip. High strength flexible spring shaft. Ideal for use with hose clips.		6



For loosening and securing nuts particularly where spanners cannot reach or are awkward to use. Tribolular handle with tapered neck for ergonomic fit. Dual material handle for comfort in use. Integral moulded finger grips around neck to allow increased torque

Nut Spinner Set - Metric

Part No	Description	Pack Size
5490	9-piece metric nut spinner set with: handle, extension piece, 9 interchangeable blades-sizes: 4, 4.5, 5, 5.5, 6, 7, 8, 9 and 10mm in high quality tool roll.	1



For loosening and securing nuts particularly where spanners cannot reach or are awkward to use. Ergonomically designed handle. Low slip textured finish for improved grip and torque