

Sefram

SEFRAM 9861

Moister Meter

**Make sure to visit
our Website**

<http://www.sefram.fr>

Ergonomic, simple and easy to use

Capabilities

- Multi-colors LED bargraph
- Bragraph with 48 LED
- Simple and easy to use
- Sturdy and durable moisture probe
- Supplied with a carrying pouch and accessories
- Analog output

Specifications SEFRAM 9861

Measure of WME (Wood Moisture Equivalent)

Ranges	5,5% à 100%
Green display	5,5% à 16%
Yellow display	17% à 21%
Red display	> 22%

Accuracy ±1% (at room temperature)

Analog output

Range	10mV / %WME Max. amplitude : 1V
Minimum load	250 ohms (min.)
Output connector	jack 3,5mm

General Specifications

Display	bargraph with 48 LED, 3 colors according to measured value
Auto power-off	yes
Operating temperature range	-20°C to 55°C (RH<70%)
Storage temperature range	-20°C to 60°C (without battery and RH<80%)
Power supply	1 single 9V battery - 6F22
Autonomy	150h typical (with alkaline batteries)
Dimensions	153 x 56 x 32 mm
Weight	145g

Supplied with : battery, manual, protecting cap.



SEFRAM 9861



FT9861A00 - Specifications can be updated without notice



32, rue Edouard Martel • B.P. 55 • 42009 - St Etienne cedex 2

0.15€ TTC/min
0 825 56 50 50

Fax. +33 (0).4.77.57.23.23

Web : www.sefram.fr • e-mail : sales@sefram.fr

For assistance and ordering