




AMP-LATCH

TE Internal #: 1658526-5
Ribbon Cable Connectors, Wire-to-Board, 10 Position, 2.54mm [.1in] Centerline, Insulation Displacement Crimp (IDC), Row-to-Row Spacing 2.54 mm [.1 in]
[View on TE.com >](#)

Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **10**
Centerline (Pitch): **2.54 mm [.1 in]**
Termination Method to Wire & Cable: **Insulation Displacement Crimp (IDC)**
Row-to-Row Spacing: **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Ribbon Cable
Number of Positions	10
Number of Rows	2

Contact Features

Wire Contact Termination Area Plating Material Thickness	2.54 – 5.08 µm[100 – 200 µin]
Wire Contact Termination Area Plating Material	Tin
	30 µin
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	1 A

Termination Features

Rectangular Termination Post & Tail Thickness	.36 mm[.014 in]
Rectangular Termination Post & Tail Width	.46 mm[.018 in]
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)



Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Color	Blue
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability









Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides



on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM74-UN384H AMP-LATCH UNIVERSAL HEADERS	 TE Part # 1-111446-4 10 UNIV I/O, NO EARS, LEAD FREE	 TE Part # 1-111504-4 10 UNIV I/O, NO EARS, LEAD FREE	 TE Part # 2-1761605-3 IDC LOW PRO HDR 10P RA BLUE
 TE Part # 1761681-3 IDC LOW PRO HDR 10P VERT HT BLACK	 TE Part # 2-1761603-3 IDC LOW PRO HDR 10P VERT BLUE	 TE Part # 1761607-3 IDC LOW PRO HDR 10P RA LG LAT	 TE Part # 1-111506-6 010 UNIV I/O 30DP SLOT LTCH
 TE Part # 1761606-3 IDC LOW PRO HDR 10P VERT LG LAT BLK	 TE Part # 2-1761711-3 IDC LOW PRO HDR 10P VERT LG LA	 TE Part # 5103309-1 A/L LOW PRO HDR 10P VERT BLACK	 TE Part # 5103308-1 A/L LOW PRO HDR 10P VERT BLACK
 TE Part # 5104340-1 A/L LOW PRO HDR 10P RA HT	 TE Part # 2-1761606-3 IDC LOW PRO HDR 10P VERT LG LAT BLUE	 TE Part # 2-1761607-3 IDC LOW PRO HDR 10P RA LG LAT	 TE Part # 1761682-3 IDC LOW PRO HDR 10P RA HT BLACK







TE Part # 3-1437020-9
609-1041=FSKT IDC S 10 30AU PL



TE Part # 1761683-3
IDC LOW PRO HDR 10P VERT HT BLACK




TE Part # 1761686-3
IDC LOW PRO HDR 10P VERT LG LAT




TE Part # 5104338-1
A/L LOW PRO HDR 10P VERT HT


Customers Also Bought




TE Part #1-1658526-1
609-1641LF FEM SOCKET,LEAD FREE



TE Part #87631-6
10 MODIV HSG DR MRKD .100 POL



TE Part #1-1658526-3
609-2041LF FEM SOCKET,LEAD FREE



TE Part #1-1658526-6
609-2641LF FEM SOCKET,LEAD FREE




TE Part #1-1337480-0
SMB FM BHSkt 50Ohm Gold Pltd




TE Part #1625873-1
RS 0402 5% RESISTOR KIT




TE Part #1337808-3
50 OHM COAX SMA STR PLUG STR P



TE Part #1487588-1
USB, A-B, 28/24, WHITE, 2.0M



TE Part #1-1337475-0
SMB Str Plg PS 50Ohm Gold Pltd RG174A/U,



TE Part #1-1478402-0
BNC Str Plg PS 50Ohm Silver RG174A /U, 18

Documents

- Product Drawings

609-1041LF FEM SOCKET,LEAD FREE

English
- CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1658526-5_C.2d_dxf.zip



English

Customer View Model

[ENG_CVM_CVM_1658526-5_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1658526-5_C.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[Ribbon Cable Interconnect Solutions](#)

English

Product Environmental Compliance

[MD_1658526-5_06052014331_dmtec](#)

English

[MD_1658526-5_06052014331_dmtec](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English