

SCLD offset steel boring bar, positive, left

For face turning and longitudinal turning using CD indexable insert

ATORN[®]



Application

For face and longitudinal turning with CD indexable insert, 80°.

Execution

- Precision-manufactured boring bar, **steel**, with internal cooling, offset, type C, attack angle 95°, tip angle 80°, clearance angle 7°

Advantage

- Universal use for face and longitudinal turning
- Positive geometry for the body ensures low cutting forces

Art. No.	17827 020
ISO name	A 0508H SCLD R/L 04
Min. bore diameter	5.8 mm
Tapered diameter	5 mm
Shaft diameter	8 mm
Clearance length	20 mm
Length	100 mm
Clamping surface height	7 mm
Programming size	2.9 mm
Suitable for indexable inserts	CD.. 0401
Tool design	Left
DIN	8024

EAN-Code

405029339 1329