Product Information Sheet

COMMISSION DELEGATED REGULATION (EU) 2019/2015 with regard to energy labelling of light sources

Supplier's name or trade mark: BRUMBERG

Supplier's address: BRUMBERG Leuchten GmbH & Co. KG , BRUMBERG Leuchten GmbH & Co. KG Hellefelder Straße 63 59846 Sundern (Germany)

Model identifier: 15311004

Type of light source:

Lighting technology used:	LED	Non-directional or directional:	DLS
Light source cap-type	wired		
(or other electric interface)			
Mains or non-mains:	NMLS	Connected light source (CLS):	Nein
Colour-tuneable light source:	Nein	Envelope:	-
High luminance light source:	Nein		
Anti-glare shield:	Nein	Dimmable:	Only with specific dimmers
	Product pa	rameters	

Product parameters						
Parameter	Value	Parameter	Value			
General product parameters:						
Energy consumption in on- mode (kWh/1000 h), rounded up to the nearest integer	99	Energy efficiency class	F			
Useful luminous flux (ϕ use), indicating if it refers to the flux in a sphere (360°), in a wide cone (120°) or in a narrow cone (90°)	7 785 in Wide cone (120°)	Correlated colour temperature, rounded to the nearest 100 K, or the range of correlated colour temperatures, rounded to the nearest 100 K, that can be set	4 000			
On-mode power (P _{on}), expressed in W	90,0	Standby power (P _{sb}), expressed in W and rounded to the second decimal	0,00			
Networked standby power (P _{net}) for CLS, expressed in W and rounded to the second decimal	-	Colour rendering index, rounded to the nearest integer, or the range of CRI- values that can be set	91			

Outer	Height	3	Spectral power	See image		
	Width	12	distribution in the	in last page		
without	Depth	5 000	range 250 nm to 800			
separate	·		nm, at full-load			
control gear,						
lighting						
control parts						
and non-						
lighting						
control parts, if any						
(millimetre)						
	nt n n		If yes, equivalent			
Claim of equivale	nt power ^(a)	-	If yes, equivalent power (W)	-		
			Chromaticity	0,375		
			coordinates (x and y)	0,371		
Parameters for d	irectional light s	sources:	· · ·			
Peak luminous in	tensity (cd)	2 668	Beam angle in	120		
			degrees, or the			
			range of beam			
			angles that can be			
			set			
Parameters for LED and OLED light sources:						
R9 colour renderi	ing index value	82	Survival factor	0,90		
the lumen maintenance factor		0,96				
(a),						

(a)'-' : not applicable;

(b)'-' : not applicable;

