

## Stepped drill bit HSS-TiN, straight groove

For universal use up to 1300 N/mm<sup>2</sup>

**ORION**<sup>®</sup>

### Application:


For drilling and simultaneous deburring in steel, stainless steel, non-ferrous metals and cast iron.

### Execution:

- Profile-ground and straight

### Advantage:

- High variability: A wide range of bores can be covered with just one tool



<b>Art. no.</b>	<b>11407 155</b>
<b>Brand</b>	ORION
<b>Manufacturer Part Number</b>	11407155
<b>Cutting material</b>	HSS
<b>Surface</b>	TiN
<b>Tool holding device</b>	Cylinder shank
<b>Type</b>	1
<b>Step diameter</b>	4 mm, 5 mm, 6 mm, 7 mm, 8 mm, 9 mm, 10 mm, 11 mm, 12 mm
<b>Step length</b>	5 mm
<b>Length</b>	79 mm
<b>Shank diameter</b>	6 mm
<b>Gross Weight</b>	0.022 kg
<b>Product Group</b>	103

### EAN

4053625030590