

Thread milling cutter solid carbide TiAlN 3xD (M, MF) straight shank HA

For hard machining up to 63 HRC in female threads

ATORN®



Application

For producing metric right-hand and left-hand threads on CNC machines in through holes and blind holes in the hardened steel material group up to a strength of 63HRC.

Version

- Thread milling cutters with short thread section

Advantage

- Innovative cutting geometry and coating technology ensure very high degree of dimensional accuracy, process reliability and chip removal
- Thread milling cutting of very small threads from M1.4 x 0.3 possible

Application	Steel (N/mm ²)			Stainless steel		Alu		Brass		Bronze		Plastics	Graphite G(C)FK	GG(G) GJMW	Titan-alloy	Nickel-alloy	Super-alloy	Hard mat.	
	<700	<1000	<1300	marten.	austen.	short	long	short	long	short	long							<55 HRC	<65 HRC
																		50	40

Art. no.	13496 997
Cutting material	VHM
Surface	TiAlN
Hole type	Clearance/blind hole ≤ 3xD
Coolant supply	External
Tool holding device	HA parallel shank
Cutting edge diameter	4.65 mm
Pitch	1 mm
Suitable for metric threads from	M6
Length	58 mm
Effective length of thread milling	20 mm
Shaft diameter	6 mm
Number of cutting edges	3 PCS
f steel 1300	0.04 mm/r

EAN-Code

4050293208009