




Connectors > PCB Connectors > Wire-to-Board Connectors > Wire-to-Board Connector Contacts



Contact Type: **Socket**
Connector System: **Wire-to-Board**
Wire Size: **.2 – .6 mm²**

Features

Product Type Features

Applied Pressure	Intermediate
Connector System	Wire-to-Board
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
-----------------------------------	---------------

Contact Features

Mating Square Post Dimension	.64 mm[.025 in]
Wire Contact Termination Area Plating Thickness	2 µm
Wire Contact Termination Area Plating Material	Tin
Contact Mating Area Plating Material Thickness	2 µm
Contact Base Material	Phosphor Bronze
Contact Type	Socket
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	3 A

Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

--	--



Accepts Wire Insulation Diameter Range	1.4 mm[.055 in]
Wire Size	.2 – .6 mm²

Usage Conditions

Operating Temperature Range	-65 – 105 °C[-85 – 221 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Power & Signal
---------------------	----------------

Packaging Features

Packaging Quantity	17500
Packaging Method	Reel

Other

Comment	For 0.63 mm "Round" Post and 0.63 x 0.63 mm "Square" Post.
---------	--

Product Compliance

For compliance documentation, visit the product page on TE.com>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 843473-1 EXTRACTION TOOL	 TE Part # 925370-5 MOD IV REC HSG 2X5P.	 TE Part # 925366-8 MOD 4 REC.HSG 1X08P	 TE Part # 925370-6 MOD.IV REC HSG, 2X6P
 TE Part # 926476-8 MOD 4 HSG	 TE Part # 926475-3 03P MODU 4 HSG.S.R.	 TE Part # 926475-4 MOD 4 HSG	 TE Part # 925369-3 MOD 4 REC.HSG 1X03P
 TE Part # 925369-6 MOD 4 REC.HSG 1X06P	 TE Part # 925370-8 MOD IV REC HSG, 2X8P	 TE Part # 925370-2 MOD IV REC HSG, 2X2P	 TE Part # 925369-2 MOD 4 REC.HSG 1X02P
 TE Part # 925370-4 MOD IV REC HSG 2X4 POS	 TE Part # 925367-4 MOD 4 REC.HSG 2X04P	 TE Part # 925369-5 MOD 4 REC.HSG 1X05P	 TE Part # 925370-3 MOD IV REC HSG, 2X3P
 TE Part # 926476-6 MOD 4 HSG	 TE Part # 1-925366-0 MOD 4 REC.HSG 1X10P	 TE Part # 1-926476-0 MOD 4 HSG	 TE Part # 5-925370-0 MOD IV REC HSG, 2X50P

Also in the Series | AMPMODU IV/V



Automotive Housings(2)	Backplane Connector Housings(1)	Board-to-Board Connector Contacts(6)	Insertion & Extraction Tools(4)
PCB Connector Covers(18)	PCB Connector Keying(6)	PCB Connector Mounting(1)	PCB Connector Strain Relief(3)
PCB Headers & Receptacles(939)	PCB Latches, Locks & Retainers(9)	Rectangular Connector Housings(5)	Standard Rectangular Connectors(8)
Wire-to-Board Connector Assemblies & Housings(467)	Wire-to-Board Connector Contacts (326)		

Documents

Product Drawings
MOD-4 REC.CONT.SCP

English

CAD Files
3D PDF

English

Customer View Model
ENG_CVM_2-167301-2_J.3d_igs.zip



English

Customer View Model

[ENG_CVM_2-167301-2_J.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_2-167301-2_J.2d_dxf.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Product Environmental Compliance

[MOD-4 REC.CONT.SCP](#)

English

[MOD-4 REC.CONT.SCP](#)

English