

LED inspection lamp with additional UV test light

With angled head, length 112 mm

ATORN[®]

Application

for illuminating and finding scratches, dirt or leaks

Version

- with two LEDs – can be switched with two separate switches.
- 1. switching: CRI 95 LED with true-colour, warm white light
- 2. switching: UV LED (black light 395 nm)
- bendable lamp head, strong magnet in the lamp base
- Protection class IP 54

Delivery

Battery included



Art. No.	56801 110
Length	112 mm
Luminous flux	70 lm
Lighting range	25 m
Material	Aluminium
Colour	Dark grey
Type of rechargeable battery/battery	Alkali
Number of rechargeable batteries/batteries	1
Rechargeable battery/battery designation	1.5 V Mignon AA

EAN-Code

405029353873 1