


Connectors > Rectangular Connectors > Rectangular Connector Accessories > Rectangular Connector Hardware



Hardware Type: **Pin Hood**

Pin Hood Type: **Internal Open End**

Connector System: **Wire-to-Wire**

Number of Positions: **15, 26**

Sealable: **No**

Features

Product Type Features

Strain Relief	Without
Product Type	Hardware
Connector System	Wire-to-Wire
Sealable	No
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Number of Positions	15, 26
---------------------	--------

Body Features

Material	Carbon Steel
----------	--------------

Contact Features

Pin Hood Type	Internal Open End
---------------	-------------------

Mechanical Attachment

Hardware Type	Pin Hood
Connector Mounting Type	Cable Mount (Free-Hanging)

Dimensions

Width	18.47 mm[.727 in]
Height	41.45 mm[1.632 in]
Length	18.23 mm[.718 in]

Usage Conditions

Operating Temperature Range	-55 – 150 °C[-67 – 302 °F]
-----------------------------	----------------------------

Operation/Application

For Use With	15 Position Mixed Connectors, 26-Position Posted Connectors, 26-Position Standard Connectors
Circuit Application	Power & Signal

Packaging Features

Packaging Quantity	1
Packaging Method	Package

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JUL 2017 (174) SVHC > Threshold: Not Yet Reviewed
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.


Customers Also Bought




TE Part #4-1879659-4
H4 3K24 0.1% 15PPM



TE Part #YACT26JE06ACV00100
Straight Plug D38999, E06 Insert



TE Part #2-87215-6
52 MODII HDR DRST UNSHRD .100



TE Part #2-87227-2
44 MODII HDR DRST UNSHRD .100



TE Part #324309-2
TERM, SPLC, BUTT, STRAT, SOLIS,
HR, 6



TE Part #532484-1
BOX JACKSCREW KIT




TE Part #201111-000
82A0111-12-F868-9



TE Part #868537-000
HEX40-AB-00-25-A12-1



TE Part #128256-000
HEX40L-AB-00-17-A6-1



TE Part #2-1589476-1
STL025SC2DC012N = WDUALOBE

Documents

Product Drawings

26 PL. PIN HOOD-FIN.

English

CAD Files

Customer View Model

[ENG_CVM_201785-4_F.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_201785-4_F.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_201785-4_F.2d_dxf.zip](#)

English

3D PDF

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[M_SERIES_PIN_AND_SOCKET_CONNECTORS](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[PIN HOODS FOR AMP SERIES "M" AND MINIATURE DUALATCH CONNECTOR BL](#)

English

Agency Approvals

[Agency Approval Document](#)

English