

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : D1 DOSEIT
Product code : 325
Type of product : Cleaning agent,Detergent
Product group : Mixture

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use,Industrial use
Industrial/Professional use spec : Industrial
For professional use only
Use of the substance/mixture : Cleaner
Degreaser

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Manufacturer

Clover Chemicals Ltd
Clover House Macclesfield Road
SK23 7DQ Whaley Bridge – Derbyshire
United Kingdom
T 01663 733114 - F 01663 733115
info@cloverchemicals.com - www.cloverchemicals.com

Supplier

Christeyns NV
Afrikalaan 182
9000 GENT
Belgium
T +32 (0)9/ 223 38 71 - F +32 (0)9/ 233 03 44
info@christeyns.be - www.christeyns.com

1.4. Emergency telephone number

Country	Official advisory body	Address	Emergency number	Comment
Ireland	National Poisons Information Centre Beaumont Hospital	PO Box 1297 Beaumont Road 9 Dublin	+353 1 809 2566 (Healthcare professionals- 24/7) +353 1 809 2166 (public, 8am - 10pm, 7/7)	
United Kingdom	National Poisons Information Service (Birmingham Centre) City Hospital	Dudley Road B18 7QH Birmingham	0344 892 0111	Only for healthcare professionals

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Skin Corr. 1 H314

Full text of hazard classes, H- and EUH-statements: see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS05

CLP Signal word : Danger
Hazard statements (CLP) : H314 - Causes severe skin burns and eye damage.
Precautionary statements (CLP) : P102 - Keep out of reach of children.
P264 - Wash hands thoroughly after handling.
P280 - Wear eye protection, protective gloves, protective clothing.
P305+P351+P338 - IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
P337+P313 - If eye irritation persists: Get medical advice/attention.
P303+P361+P353 - IF ON SKIN (or hair): Take off immediately all contaminated clothing.

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Rinse skin with water or shower.

P332+P313 - If skin irritation occurs: Get medical advice/attention.

2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

Contains no PBT/vPvB substances $\geq 0.1\%$ assessed in accordance with REACH Annex XIII

Component	
Isotridecanol, ethoxylated (69011-36-5)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII
Poly(oxy-1,2-ethanediyl), alpha-(2-propylheptyl)-omega-hydroxy- (160875-66-1)	This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

The mixture does not contain substance(s) included in the list established in accordance with Article 59(1) of REACH for having endocrine disrupting properties, or is not identified as having endocrine disrupting properties in accordance with the criteria set out in Commission Delegated Regulation (EU) 2017/2100 or Commission Regulation (EU) 2018/605

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
3-butoxy-2-propanol	CAS-no: 5131-66-8 Einecs nr: 225-878-4 EG annex nr: 603-052-00-8 REACH-no: 01-2119475527-28	3 – 5	Eye Irrit. 2, H319 Skin Irrit. 2, H315
Isotridecanol, ethoxylated	CAS-no: 69011-36-5 REACH-no: polymer	1 – 3	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318
Beta-alanine, N-(2-carboxyethyl)-,N-coco alykyl derivs., disodium salts	CAS-no: 90170-43-7 Einecs nr: 290-476-8 REACH-no: 01-2119976233-35	1 – 3	Eye Irrit. 2, H319
Poly(oxy-1,2-ethanediyl), alpha-(2-propylheptyl)-omega-hydroxy-	CAS-no: 160875-66-1 Einecs nr: 605-233-7 REACH-no: exemption polymer	1 – 3	Acute Tox. 4 (Oral), H302 Eye Dam. 1, H318
Sodium hydroxide substance with national workplace exposure limit(s) (IE, GB)	CAS-no: 1310-73-2 Einecs nr: 215-185-5 EG annex nr: 011-002-00-6 REACH-no: 01-2119457892-27	1 – 3	Skin Corr. 1A, H314 Eye Dam. 1, H318 Met. Corr. 1, H290

Specific concentration limits:

Name	Product identifier	Specific concentration limits
Poly(oxy-1,2-ethanediyl), alpha-(2-propylheptyl)-omega-hydroxy-	CAS-no: 160875-66-1 Einecs nr: 605-233-7 REACH-no: exemption polymer	(1 \leq C \leq 10) Eye Irrit. 2, H319 (10 < C \leq 100) Eye Dam. 1, H318
Sodium hydroxide	CAS-no: 1310-73-2 Einecs nr: 215-185-5 EG annex nr: 011-002-00-6 REACH-no: 01-2119457892-27	(0.5 \leq C < 2) Eye Irrit. 2, H319 (0.5 \leq C < 2) Skin Irrit. 2, H315 (2 \leq C < 5) Skin Corr. 1B, H314 (5 \leq C < 100) Skin Corr. 1A, H314

Full text of H- and EUH-statements: see section 16

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 4: First aid measures

4.1. Description of first aid measures

General advice	: Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
Inhalation	: Allow affected person to breathe fresh air. Allow the victim to rest.
Skin contact	: Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
Eye contact	: Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
Ingestion	: Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

Acute effects inhalation	: May cause irritation to the respiratory tract, sneezing, coughing, burning sensation of throat with constricting sensation of the larynx and difficulty in breathing.
Acute effects skin	: Causes skin irritation. Red skin.
Acute effects eyes	: Causes serious eye damage. redness, itching, tears. Risk of serious damage to eyes.
Acute effects oral route	: Burns or irritation of the linings of the mouth, throat, and gastrointestinal tract. Abdominal pain, nausea.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media : Water.

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire : Toxic fumes may be released. Carbon dioxide. Carbon monoxide.

5.3. Advice for firefighters

Firefighting instructions	: Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment.
Protection during firefighting	: Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures : Mark the danger area. Wear recommended personal protective equipment.

6.1.1. For non-emergency personnel

Protective equipment	: Use personal protective equipment as required.
Emergency procedures	: Evacuate unnecessary personnel.

6.1.2. For emergency responders

Protective equipment	: Equip cleanup crew with proper protection.
Emergency procedures	: Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Section 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed	: Avoid all unnecessary exposure.
Precautions for safe handling	: Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	: Store in a cool, well-ventilated place. Keep container tightly closed. Keep only in original container.
Incompatible products	: Strong acids.
Packaging materials	: polyethylene. stainless steel.

7.3. Specific end use(s)

No additional information available

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

8.1.1 National occupational exposure and biological limit values

Sodium hydroxide (1310-73-2)	
Ireland - Occupational Exposure Limits	
Local name	Sodium hydroxide
OEL STEL	2 mg/m ³
Regulatory reference	Chemical Agents Code of Practice 2021
United Kingdom - Occupational Exposure Limits	
Local name	Sodium hydroxide
WEL STEL (OEL STEL)	2 mg/m ³
Regulatory reference	EH40/2005 (Fourth edition, 2020). HSE

8.1.2. Recommended monitoring procedures

No additional information available

8.1.3. Air contaminants formed

No additional information available

8.1.4. DNEL and PNEC

No additional information available

8.1.5. Control banding

No additional information available

8.2. Exposure controls

8.2.1. Appropriate engineering controls

Appropriate engineering controls:

Ensure that there is a suitable ventilation system.

8.2.2. Personal protection equipment

Personal protective equipment:

Gloves. Protective clothing. Protective goggles. Avoid all unnecessary exposure.

Personal protective equipment symbol(s):



8.2.2.1. Eye and face protection

Eye protection:

tightly fitting safety goggles. Chemical goggles or safety glasses

8.2.2.2. Skin protection

Protective equipment:

Protective clothing

Hand protection:

Wear protective gloves.

8.2.2.3. Respiratory protection

No additional information available

8.2.2.4. Thermal hazards

No additional information available

8.2.3. Environmental exposure controls

Other information:

Do not eat, drink or smoke during use.

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Liquid
Colour	: Blue.
Physical state/form	: Liquid.
Odour	: Characteristic.
Odour threshold	: Not available
Melting point/range	: 0 °C
Freezing point	: Not available
Boiling point/Boiling range	: 100 °C
Flammability	: Non flammable.
Explosive limits	: Not available
Lower explosion limit	: Not available
Upper explosion limit	: Not available
Flash point	: Not available
Autoignition temperature	: Not available
Decomposition temperature	: Not available
pH	: 13 – 14
Viscosity, kinematic	: Not available
Solubility	: Soluble in water.
Partition coefficient n-octanol/water (Log Kow)	: Not available
Vapour pressure	: Not available
Vapour pressure at 50 °C	: Not available
Density	: Not available
Relative density	: 1.055
Relative vapour density at 20 °C	: Not available
Particle characteristics	: Not applicable

9.2. Other information

9.2.1. Information with regard to physical hazard classes

No additional information available

9.2.2. Other safety characteristics

VOC content : 57.3 g/l

SECTION 10: Stability and reactivity

10.1. Reactivity

Stable under normal conditions.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures.

10.5. Incompatible materials

Strong acids.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

Poly(oxy-1,2-ethanediyl), alpha-(2-propylheptyl)-omega-hydroxy- (160875-66-1)

LD50 oral rat	500 – 2000 mg/kg
---------------	------------------

3-butoxy-2-propanol (5131-66-8)

LD50 oral rat	3300 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 401 (Acute Oral Toxicity), 95% CL: 2800 - 4500
---------------	---

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

3-butoxy-2-propanol (5131-66-8)	
LD50 dermal rat	> 2000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 402 (Acute Dermal Toxicity)
LC50 Inhalation - Rat (Vapours)	35 mg/l/4h
Skin corrosion/irritation	: Causes severe skin burns. pH: 13 – 14
Serious eye damage/irritation	: Assumed to cause serious eye damage pH: 13 – 14
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
3-butoxy-2-propanol (5131-66-8)	
LOAEL (oral, rat, 90 days)	1000 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents), Guideline: EU Method B.26 (Sub-Chronic Oral Toxicity Test: Repeated Dose 90-Day Oral Toxicity Study in Rodents)
NOAEL (oral, rat, 90 days)	350 mg/kg bodyweight Animal: rat, Guideline: OECD Guideline 408 (Repeated Dose 90-Day Oral Toxicity in Rodents), Guideline: EU Method B.26 (Sub-Chronic Oral Toxicity Test: Repeated Dose 90-Day Oral Toxicity Study in Rodents)
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met
11.2. Information on other hazards	
11.2.1. Endocrine disrupting properties	
No additional information available	
11.2.2. Other information	
Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met
SECTION 12: Ecological information	
12.1. Toxicity	
Hazardous to the aquatic environment, short-term (acute)	: Not classified
Hazardous to the aquatic environment, long-term (chronic)	: Not classified
Not rapidly degradable	
Sodium hydroxide (1310-73-2)	
LC50 - Fish [1]	> 35 mg/l
EC50 - Crustacea [1]	40.4 mg/l (Ceriodaphnia)
EC50 - Other aquatic organisms [1]	> 33 mg/l waterflea
Poly(oxy-1,2-ethanediyl), alpha-(2-propylheptyl)-omega-hydroxy- (160875-66-1)	
EC50 - Crustacea [1]	≥ 10 (10 – 100) mg/l
3-butoxy-2-propanol (5131-66-8)	
LC50 - Fish [1]	> 560 mg/l Poecilia reticulata (Guppy)
EC50 - Crustacea [1]	> 1000 mg/l

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

12.2. Persistence and degradability

D1 DOSEIT	
Persistence and degradability	Biodegradable. The surfactant(s) contained in this preparation complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them, at their direct request or at the request of a detergent manufacturer.
Sodium hydroxide (1310-73-2)	
Persistence and degradability	Not applicable.
3-butoxy-2-propanol (5131-66-8)	
Biodegradation	90 % (28 d)

12.3. Bioaccumulative potential

D1 DOSEIT	
Bioaccumulative potential	No bioaccumulation.
Sodium hydroxide (1310-73-2)	
Log Pow	-3.88
Bioaccumulative potential	No bioaccumulation.

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

D1 DOSEIT	
This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII	
This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII	

12.6. Endocrine disrupting properties

No additional information available

12.7. Other adverse effects

Additional information : Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations.

Waste / unused products : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA

ADR	IMDG	IATA
14.1. UN number or ID number		
Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name		
Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)		
Not regulated	Not regulated	Not regulated
14.4. Packing group		
Not regulated	Not regulated	Not regulated
14.5. Environmental hazards		
Not regulated	Not regulated	Not regulated
No supplementary information available		

14.6. Special precautions for user

Overland transport

Not regulated

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Transport by sea

Not regulated

Air transport

Not regulated

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to Regulation (EU) No 649/2012 of the European Parliament and of the Council of 4 July 2012 concerning the export and import of hazardous chemicals.

Contains no substance subject to Regulation (EU) No 2019/1021 of the European Parliament and of the Council of 20 June 2019 on persistent organic pollutants

Contains no substance subject to REGULATION (EU) No 1005/2009 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 September 2009 on substances that deplete the ozone layer.

Contains no substance subject to Regulation (EU) 2019/1148 of the European Parliament and of the Council of 20 June 2019 on the marketing and use of explosives precursors.

VOC content : 57.3 g/l

Detergent Regulation (648/2004/EC): Labelling of contents:

Component	%
non-ionic surfactants, amphoteric surfactants	<5%

Contains no substance subject to Regulation (EC) 273/2004 of the European Parliament and of the Council of 11 February 2004 on the manufacture and the placing on market of certain substances used in the illicit manufacture of narcotic drugs and psychotropic substances.

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

Acute Tox. 4 (Oral)	Acute toxicity (oral), Category 4
Eye Dam. 1	Serious eye damage/eye irritation, Category 1
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
H290	May be corrosive to metals.
H302	Harmful if swallowed.
H314	Causes severe skin burns and eye damage.
H315	Causes skin irritation.
H318	Causes serious eye damage.
H319	Causes serious eye irritation.
Met. Corr. 1	Corrosive to metals, Category 1
Skin Corr. 1	Skin corrosion/irritation, Category 1
Skin Corr. 1A	Skin corrosion/irritation, Category 1, Sub-Category 1A

D1 DOSEIT

Safety Data Sheet

according to the REACH Regulation (EC) 1907/2006 amended by Regulation (EU) 2020/878

Full text of H- and EUH-statements:

Skin Corr. 1B	Skin corrosion/irritation, Category 1, Sub-Category 1B
Skin Irrit. 2	Skin corrosion/irritation, Category 2

Classification and procedure used to derive the classification for mixtures according to Regulation (EC) 1272/2008 [CLP]:

Skin Corr. 1	H314	On basis of test data
--------------	------	-----------------------

Safety Data Sheet (SDS), EU

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.