


AMP-LATCH

TE Internal #: 1658526-2
Ribbon Cable Connectors, Wire-to-Board, 6 Position, 2.54mm [.1in]
Centerline, Insulation Displacement Crimp (IDC), Row-to-Row
Spacing 2.54 mm [.1 in]

[View on TE.com >](#)



Connectors > PCB Connectors > Wire-to-Board Connectors > FFC, FPC & Ribbon Connectors > Ribbon Cable Connectors



Connector System: **Wire-to-Board**
Number of Positions: **6**
Centerline (Pitch): **2.54 mm [.1 in]**
Termination Method to Wire & Cable: **Insulation Displacement Crimp (IDC)**
Row-to-Row Spacing: **2.54 mm [.1 in]**

Features

Product Type Features

Connector Product Type	Connector Assembly
Connector System	Wire-to-Board
Connector & Housing Type	Receptacle
Connector & Contact Terminates To	Wire & Cable

Configuration Features

Compatible With Wire & Cable Type	Ribbon Cable
Number of Positions	6
Number of Rows	2

Contact Features

Wire Contact Termination Area Plating Material Thickness	2.54 – 5.08 μm[100 – 200 μin]
Wire Contact Termination Area Plating Material	Tin
	30 μin
Contact Mating Area Plating Material	Gold
Contact Current Rating (Max)	1 A



Termination Features

Rectangular Termination Post & Tail Thickness	.36 mm[.014 in]
Rectangular Termination Post & Tail Width	.46 mm[.018 in]
Termination Method to Wire & Cable	Insulation Displacement Crimp (IDC)

Mechanical Attachment

Mating Alignment Type	Polarization
Mating Retention	Without
Connector Mounting Type	Cable Mount (Free-Hanging)

Housing Features

Housing Color	Blue
Centerline (Pitch)	2.54 mm[.1 in]

Dimensions

Row-to-Row Spacing	2.54 mm[.1 in]
--------------------	----------------

Usage Conditions

Operating Temperature Range	-55 – 125 °C[-67 – 257 °F]
-----------------------------	----------------------------

Operation/Application

Circuit Application	Signal
---------------------	--------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2021 (211) Candidate List Declared Against: JAN 2021 (211) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability







Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as





EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

 TE Part # CAT-AM71-UN385 Universal Headers: Ejector Latch	 TE Part # 2-1761603-1 IDC LOW PRO HDR 6P VERT BLUE	 TE Part # 2-1761605-1 IDC LOW PRO HDR 6P RA BLUE	 TE Part # 2-1761607-1 IDC LOW PRO HDR 6P RA LG LAT B
 TE Part # 2-1761606-1 IDC LOW PRO HDR 6P VERT LG LAT	 TE Part # 2-1761679-1 IDC LOW PRO HDR 6P VERT BLUE	 TE Part # 3-1761603-2 IDC LOW PRO HDR 36P VERT BLUE	 TE Part # 1761681-1 IDC LOW PRO HDR 6P VERT HT BLACK
 TE Part # 2-1761711-1 IDC LOW PRO HDR 6P VERT LG LAT			

Customers Also Bought

 TE Part #1717254-1 DDR2 SO DIMM Sockets	 TE Part #1-1658526-2 609-2030LF FEM SOCKET, LEAD FREE	 TE Part #1658526-1 609-0630LF FEM SOCKET, LEAD FREE	 TE Part #1648325-1 702-92-01109=CONTACT, SKT, #20
--	---	--	--






TE Part #1-2201864-2
Mini I/O Receptacle Kit Type 2 Piercing



TE Part #1676247-1
RN 0805 200R 0.1% 10PPM CUT LENGTH



TE Part #141603-3
MOD-4 REC.CONTACT



TE Part #1-2176245-0
CRGS1206 5% 5R6



TE Part #1-1879138-0
RN 0603 1K91 0.1% 10PPM 5K RL



TE Part #8-31886-1
PIDG RING TONGUE TERMINALS

Documents

Product Drawings
609-0641LF FEM SOCKT,LEAD FREE
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1658526-2_C.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1658526-2_C.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1658526-2_C.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages
Ribbon Cable Interconnect Solutions
English

Product Environmental Compliance
TE Material Declaration
English

Instruction Sheets
Instruction Sheet (U.S.)



English