




## Diffuse mode sensor OBD600-18GM40-E0



- Strong metallic housing in cylindrical shape M18 x 1
- Operating distance adjustable
- Not sensitive to ambient light
- Degree of protection IP67
- High operating distance


### Diffuse mode sensor



### Function

The optical sensors of this series have an M18 threaded housing that is optionally available in plastic or metal. The sensors are robust and versatile. Focusing on the essential requirements simplifies selection and commissioning, saving time and costs.

### Dimensions



### Technical Data

#### General specifications

|                            |                                |
|----------------------------|--------------------------------|
| Detection range            | 0 ... 600 mm                   |
| Detection range min.       | 0 ... 30 mm                    |
| Detection range max.       | 0 ... 600 mm                   |
| Adjustment range           | 30 ... 600 mm                  |
| Reference target           | standard white 200 mm X 200 mm |
| Light source               | LED                            |
| Light type                 | modulated visible red light    |
| Diameter of the light spot | approx. 40 mm at 600 mm        |
| Opening angle              | approx. 2.6 °                  |
| Optical face               | frontal                        |
| Ambient light limit        | EN 60947-5-2 20000 Lux         |
| Hysteresis                 | H < 15 %                       |

Release date: 2022-05-12 Date of issue: 2022-05-12 Filename: 70113328-100105\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

Pepperl+Fuchs Group  
www.pepperl-fuchs.com

USA: +1 330 486 0001  
fa-info@us.pepperl-fuchs.com

Germany: +49 621 776 1111  
fa-info@de.pepperl-fuchs.com


Singapore: +65 6779 9091  
fa-info@sg.pepperl-fuchs.com

**PF** PEPPERL+FUCHS


## Technical Data

| Functional safety related parameters |                |  |
|--------------------------------------|----------------|--|
| MTTF <sub>d</sub>                    |                | 1289 a   |
| Mission Time (T <sub>M</sub> )       |                | 20 a   |
| Diagnostic Coverage (DC)             |                | 0 %  |
| Indicators/operating means           |                |  |
| Operation indicator                  |                | LED green:<br>on - power on<br>flashing (4 Hz) - short circuit                         |
| Function indicator                   |                | LED yellow:<br>constantly on - object detected<br>constantly off - object not detected |
| Control elements                     |                | sensitivity adjustment   |
| Electrical specifications            |                |  |
| Operating voltage                    | U <sub>B</sub> | 10 ... 30 V DC   |
| Ripple                               |                | max. 10 %  |
| No-load supply current               | I <sub>0</sub> | < 25 mA  |
| Protection class                     |                | III  |
| Output                               |                |  |
| Switching type                       |                | Q - Pin4: NPN normally open / light-on   |
| Signal output                        |                | 1 NPN output, short-circuit protected, reverse polarity protected, open collector      |
| Switching voltage                    |                | max. 30 V DC   |
| Switching current                    |                | max. 100 mA , resistive load   |
| Voltage drop                         | U <sub>d</sub> | ≤ 1.5 V DC   |
| Switching frequency                  | f              | 500 Hz   |
| Response time                        |                | ≤ 1 ms   |
| Conformity                           |                |  |
| Product standard                     |                | EN 60947-5-2   |
| Approvals and certificates           |                |  |
| UL approval                          |                | E87056 , cULus Listed , class 2 power supply , type rating 1                           |
| Ambient conditions                   |                |  |
| Ambient temperature                  |                | -40 ... 60 °C (-40 ... 140 °F)   |
| Storage temperature                  |                | -40 ... 70 °C (-40 ... 158 °F)   |
| Mechanical specifications            |                |  |
| Degree of protection                 |                | IP67   |
| Connection                           |                | 2 m fixed cable  |
| Material                             |                |  |
| Housing                              |                | brass, nickel-plated   |
| Optical face                         |                | PMMA   |
| Cable                                |                | PVC  |
| Mass                                 |                | approx. 60 g   |

## Connection






Indication



|   |                        |        |
|---|------------------------|--------|
| 1 | Operating display      | green  |
| 2 | Signal display         | yellow |
| 3 | Sensitivity adjustment |        |
| 4 | Emitter                |        |
| 5 | Receiver               |        |






Characteristic Curve



Release date: 2022-05-12 Date of issue: 2022-05-12 Filename: 70113328-100105\_eng.pdf

Refer to "General Notes Relating to Pepperl+Fuchs Product Information".

## Accessories

|   |                 |   |
|---|-----------------|---|
|  | <b>CPZ18B03</b> | Mounting Bracket with swivel nut  |
|  | <b>BF 18-F</b>  | Plastic mounting adapter, 18 mm   |
|  | <b>BF 5-30</b>  | Universal mounting bracket for cylindrical sensors with a diameter of 5 ... 30 mm |
|  | <b>BF 18</b>    | Mounting flange, 18 mm  |
|  | <b>OMH-04</b>   | Mounting aid for round steel $\varnothing$ 12 mm or sheet 1.5 mm ... 3 mm         |