

3-point internal micrometer

IMICRO



Application:

For high-precision measurement of through-bores, even at high measuring depths.

Execution:

- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning

Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

Delivery:

In cardboard box



| | |
|---|--------------------------------|
| Art. no. | 31695 003 |
| Brand | TESA |
| Manufacturer Part Number | 00813410 |
| Min./max. length measuring range | 3.5-4 mm |
| Measuring depth | 20 mm |
| Error limit | 4 µm |
| Vernier scale | 0.001 mm |
| Measuring spindle increments | 0.5 mm |
| Calibration Group | I |
| DIN | 863 |
| Calibration Group Description | Internal micrometers (3 point) |
| Gross Weight | 0.300 kg |
| Product Group | 362 |

EAN

7630041108330