



Product Data Sheet

145X552

Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

380 Amps 600 Volts AC/DC

Wire Range

- Line: (1) 500kcmil - #4 AWG
- Load: (12) #2 - #14 AWG

Electrical Ratings

- 380 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- Short circuit current ratings (SCCR): See SCCR section below for specifications.
- CU9 - 90°C connector terminal rating with copper
- Factory & Field Wiring


Agency Compliance

- UR - UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA - certified to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1

Material Information

- Insulator base:
 - Phenolic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 150°C (UL RTI)
- Connector: copper, tin plated
- Terminal set screws: aluminum, tin plated
- Connector mounting screws: steel, zinc plated
- RoHS compliant

Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	500 kcmil	42.4 N·m (375 lbf·in)	1	B, C
	400 - 2	42.4 N·m (375 lbf·in)	1	B, C, G, H, I (DLO)
	4	42.4 N·m (375 lbf·in)	1	B, C

- Aluminum wire range: 500kcmil - 4 AWG
- Wire strip length: 1 5/16 in. (33mm)
- Terminal screw drive: 3/8 in. hex

Load Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) ¹
	2 AWG	5.6 N·m (50 lbf·in)	1	B, C
	4 - 6	5.1 N·m (45 lbf·in)	1	B, C, G, H, I (DLO)
	8	4.5 N·m (40 lbf·in)	1 - 2 ²	B, C, G, H, I (DLO)
	10	4 N·m (35 lbf·in)	1 - 2	B, C, I (DLO)
	12 - 14	4 N·m (35 lbf·in)	1 - 2	I (DLO)
1 - 4			B, C	

- Solid copper wire range: 10 - 14
- Aluminum wire range: 2 - 14 AWG
- Wire strip length:
 - top row: 3/4 in. (19mm)
 - bottom row: 1 3/16 in. (30mm)
- Terminal screw drive: slotted

¹ For information on copper stranded wire classes please visit:
<http://www.marathonsp.com/flexible-stranded-wire.php>

² Multiple wire rating applies to class B, C, & I.

Short Circuit Current Ratings (SCCR)

- The suitable conductor ranges are limited to the table values only for achieving the SCCR in excess of the default rating of 10,000A.
- Other conductor combinations within the “Terminal Specifications” noted are suitable for achieving a SCCR of 10,000A (the default rating of terminal blocks).
- Enclosure size – Investigated with a minimum 16x12x6 enclosure. Use in smaller enclosures is subject to end use evaluation.

SCCR With Fuses

Wire Class	Suitable Conductors		Max Overcurrent Protection Fuse Required Amp Rating / Class						SCCR RMS Sym. Amps 600V. Max
	Line	Load	J	T	RK1	RK5	G	CC	
B, C	500 - 3/0	2 - 6	400	400	400	200	60	30	100,000
B, C	500 - 4	2 - 10	250	250	200	100	60	30	100,000
G, H, I	350 - 2	4 - 6	400	400	400	200	60	30	100,000
G, H, I	350 - 2	4 - 10	250	250	200	100	60	30	100,000
(*)	500 - 4	2 - 14	None						10,000

* Any wire class evaluated (see terminal specification section)

SCCR With Circuit Breakers

Suitable		Overcurrent Protection		Max AMP	Volts Max	SCCR RMS Sym. Amps 600V. Max
Line	Load	MFR	TYPE			
2/0 - 4	2 - 8	Square-D	JDL36250	250	480	18,000
		Square-D	JGL36250	250	480	35,000
		Square-D	JJL36250	250	480	65,000
		Square-D	JLL36250	250	480	65,000
350 - 4	2 - 10	Allen Bradley	140U-J3D3	250	480	35,000
500 - 4	2 - 8	Allen Bradley	140U-J3D3	400	480	35,000
500 - 2	2 - 6	Allen Bradley	140G-K3 140G-K6 140G-K0 140G-K15 140MG-K8	400	480	35,000
350 - 4	2 - 10	Allen Bradley	140G-J3D3	250	480	35,000
350 - 4	2 - 10	Allen Bradley	140G-J3 140G-J6 140G-J0 140G-J15 140MG-J8	250	480	35,000
500 - 4	2 - 6	Allen Bradley	140U-K3D3	400	480	35,000

Installation & Accessories

- Mounting (Panel):
 - For use with 1/4 fastener.
 - Recommended mounting torque, 30-40 lb-in.
- Covers:
 - Flat covers available upon request
 - Catalog Number: CC 145x (replace "x" with number of poles)
 - Covers are clear polycarbonate
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications.

Drawing

