

## Pneumatic straight grinder G 551 D

**MANNESMANN  
DEMAG**

### Application:

Specially designed for fine milling, grinding, engraving and polishing work

### Execution:

- Ergonomic design
- Rear exhaust via hose unit with integrated silencer
- High speed for excellent machining quality

### Advantage:

- High degree of concentricity for long run-times

### Delivery:

Includes hose unit and collet chuck keys



<b>Art. no.</b>	<b>75061 060</b>
<b>Brand</b>	MANNESMANN DEMAG
<b>Manufacturer Part Number</b>	29939855
<b>Valve design</b>	Rotary valve
<b>Max. idle speed</b>	55000 rpm
<b>Min./max. idle speed</b>	0-55000 rpm
<b>Power output</b>	100 W
<b>Air consumption</b>	2 l/s
<b>Sound-pressure level</b>	74 dB
<b>Length</b>	120 mm
<b>Diameter of housing</b>	14 mm
<b>Collet chuck diameter</b>	3 mm
<b>Suitable for max. sanding block diameter</b>	8 mm
<b>Max. HM rotating milling cutter diameter</b>	6 mm
<b>Weight</b>	0.15 kg
<b>Gross Weight</b>	0.568 kg
<b>Product Group</b>	7AA

### EAN

4251757300004