

ROLINE LineSecure II 1500R

Product No.	19.40.1119
Manufacturer	ROLINE
Manufacturer No.	19.40.1119
EAN (single piece)	7611990979752



LineSecure UPS's work with the "buck & boost" line interactive technology; used when reliable protection against strong voltage fluctuations is essential. Protect against: power failure, power sag, power surge, under voltage, over voltage.

Product features:

- Compact, quiet, user friendly
- Desktop and 19" RM models
- Short circuit and overload protection
- AVR (Automatic Voltage Regulation)
- ABM (Automatic Battery Management) increases battery life up to 50%
- Telephone/Modem connections
- Shutdown software including License for 1 server
- Serial Port for advanced Power Management Software (incl, in content of delivery)
- UPS Management Software : Windows NT/ 2k / XP / 7 / 8 /Server 2003 / 2008 / 2012 x86/x64, MAC OS X (Intel) 10.6.x, 10.7.x, 10.8.x Mountain Lion, 10.9.x MavericksMAC OS, LINUX
- Content: UPS, Cable set, Software CD

Technical specifications	
Manufacturer	ROLINE
Product group	UPS
Product type	UPS Line Interactive, Rackmount

Colour	black
Scope of delivery	UPS, software, cable set
Classification (IEC 62040-3)	VI-SS-333
UPS technology	Line Interactive
Power class	1000 ... 1900 VA
Output (VA/W)	1500 / 960
Efficiency	95 %
Backup time	3 min
Backup time full/half-load	3 / 6 min
Weight	25 kg
Dimensions (HxWxD)	130 x 483 x 381 mm
Mounting form	Rackmount
Voltage (input)	230V +- 15%
Voltage (output)	230V
Frequency	50Hz
Connector type (input)	Cold connector IEC320 C14
Outputs	4
Connector type (output)	4x cold connector IEC320 C13
Phase in/output	230V/230V / 50Hz
Over current protection	EMI,- RFI-Filter
Max. quantity of delay expansion units	0
Delay expansion unit	--
Slots for adapter card	0
Slot for adapter card	--
Interface	USB, RS232
RS-232 Interface	Yes
USB 2.0 Interface	Yes
Hot swap batteries	No

Bypass	No
Additional over current protector	Telephone/Fax
Activity	Display
Activity Display	LCD
incl.Management Software	Windows
Internal cooling	Active, fan
Ambient temperature	0-40°C