


SPREIZBLINDNIETE FLACHRUNDKOPF


PEEL BLIND RIVETS DOMED HEAD

RIVETS ÉCLATÉS TÊTE PLATE



Aluminium AIMG 5
Aluminium AIMG 5
Aluminium AIMG 5

Stahl verzinkt
Steel zinc plated
Acier zingué



Ø 3,2 mm

D1 = 3,2 + / - 0,08 mm
D2 = 6,0 + / - 0,24 mm
k = 0,8 + 0,2 / - 0 mm
d = 1,9 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm

3,5 - 3,7 mm

	F-Max		CODE					
	3,2 x 8,0 mm	12,0 mm	0,5 - 1,0 mm	70883 20800	765 N	700 N	1000	10000
	3,2 x 10,0 mm	14,0 mm	1,0 - 3,0 mm	70883 21000			1000	10000
	3,2 x 12,0 mm	16,0 mm	3,0 - 5,0 mm	70883 21200			1000	10000
	3,2 x 16,0 mm	20,0 mm	7,0 - 9,0 mm	70883 21600			1000	10000

Ø 4,0 mm

D1 = 4,0 + 0,8 / - 0,15 mm
D2 = 8,0 + 0 / - 0,3 mm
k = 1,2 + / - 0,2 mm
d = 2,3 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm

4,3 - 4,5 mm

	F-Max		CODE					
	4,0 x 10,0 mm	14,0 mm	1,5 - 5,0 mm	70884 01000	1260 N	1150 N	1000	10000
	4,0 x 12,0 mm	16,0 mm	4,0 - 6,5 mm	70884 01200			1000	10000
	4,0 x 14,0 mm	18,0 mm	6,0 - 9,0 mm	70884 01400			500	5000
	4,0 x 16,0 mm	20,0 mm	8,0 - 11,0 mm	70884 01600			500	5000
	4,0 x 18,0 mm	22,0 mm	10,0 - 13,0 mm	70884 01800			500	5000
	4,0 x 20,0 mm	24,0 mm	12,0 - 15,0 mm	70884 02000			500	5000
	4,0 x 25,0 mm	29,0 mm	15,0 - 20,0 mm	70884 02500			500	5000
	4,0 x 30,0 mm	34,0 mm	20,0 - 25,0 mm	70884 03000			500	5000

Ø 4,8 mm

D1 = 4,8 + 0,08 / - 0,15 mm
D2 = 9,5 + / - 0,3 mm
k = 1,3 + / - 0,2 mm
d = 2,6 mm
P = ≥ 27,0 mm
L = + 1,0 / - 0,2 mm

5,1 - 5,3 mm

	F-Max		CODE					
	4,8 x 10,0 mm	14,5 mm	0,5 - 4,0 mm	70884 81000	2000 N	1720 N	500	5000
	4,8 x 14,0 mm	18,5 mm	4,0 - 8,0 mm	70884 81400			500	5000
	4,8 x 18,0 mm	22,5 mm	8,0 - 12,0 mm	70884 81800			500	5000
	4,8 x 22,0 mm	26,5 mm	12,0 - 16,0 mm	70884 82200			500	5000
	4,8 x 25,0 mm	29,5 mm	16,0 - 19,0 mm	70884 82500			500	5000
	4,8 x 30,0 mm	34,5 mm	19,0 - 24,0 mm	70884 83000			250	2500
	4,8 x 35,0 mm	39,5 mm	24,0 - 29,0 mm	70884 83500			250	2500
	4,8 x 40,0 mm	44,5 mm	29,0 - 34,0 mm	70884 84000			250	2500
	4,8 x 45,0 mm	49,5 mm	34,0 - 39,0 mm	70884 84500			250	2500
	4,8 x 50,0 mm	54,5 mm	39,0 - 44,0 mm	70884 85000			250	2500