

## Horizontal quick-action clamp

With open clamping arm and horizontal base



### Application:

For quick clamping of workpieces.

### Execution:

- Galvanised and passivated
- Ergonomic, oil-resistant handle with large hand rest and soft components.
- Case-hardened and lubricated bearing bushes

### Delivery:

With thrust bolt and protective cap



<b>Art. no.</b>	<b>26215 040</b>
<b>Brand</b>	AMF
<b>Manufacturer Part Number</b>	93047
<b>Size</b>	4
<b>Hole distance</b>	41 mm
<b>Min./max. distance between stop and centre of drill</b>	29-43 mm
<b>Bore diameter</b>	8.5 mm
<b>Clamping height</b>	45 mm
<b>Retaining force</b>	2000 N
<b>Max. tensile force</b>	3000 N
<b>Height</b>	75 mm
<b>Length 2</b>	287 mm
<b>Thumbscrew size</b>	M8 x 65 mm
<b>Gross Weight</b>	0.840 kg
<b>Product Group</b>	260

### EAN

4020772093044