

## CKUN steel boring bar, negative, left

for longitudinal turning with KN indexable insert

**ATORN**<sup>®</sup>

### Application

For longitudinal turning using KN 55° indexable insert.

### Version

- precision-manufactured steel boring bar, K type, 93° pitch angle, 55° tip angle, 0° clearance angle

### Advantage

- optimised geometry for low-performance machines
- positive cutting geometry of the indexable insert ensures low cutting forces
- wide range of delivery: suitable for both finishing and roughing



<b>Art. No.</b>	<b>17851 011</b>
<b>ISO name</b>	S 25 T CKUN R/L 16
<b>Min. bore diameter</b>	37 mm
<b>Shaft diameter</b>	25 mm
<b>Clearance length</b>	50 mm
<b>Length</b>	300 mm
<b>Clamping surface height</b>	23 mm
<b>Programming size</b>	20.5 mm
<b>Suitable for indexable inserts</b>	KNUX 1604..
<b>Tool design</b>	Left
<b>DIN</b>	8024

### EAN-Code

4050293127515