



Model Number


IQC22-22-T9 50pcs

Data carrier

Features

- Operating frequency 13.56 MHz
- Conforms to ISO 15693
- 64 bit Fixcode
- 2 kBit memory available
- Readable and writable from both sides
- Protection degree IP68
- With extended temperature range up to 220 °C (428 °F)
- Fix code lasered onto housing

Dimensions



Technical data

General specifications

Operating frequency	13.56 MHz
Transfer rate	26 kBit/s

Memory

Chip Type	Tag-it HF-I Plus (Texas Instruments)
Type/Size	EEPROM 2 kBit ROM 64 Bit
Read cycles	unlimited
Write cycles	> 100000
Data retention period	10 years at 25 °C (77 °F)

Ambient conditions

Ambient temperature	-25 ... 90 °C (-13 ... 194 °F)
Storage temperature	-25 ... 120 °C (-13 ... 248 °F) 160 °C (433 K) for 50 hours 220 °C (493 K) for 30 seconds
Climatic conditions	Isostatic water pressure: 45 bar for 10 hours
Shock and impact resistance	Oscillation (sinus): 10 g, 10 - 2000 Hz in accordance with EN 60068-2-6 Shock (semi-sinus): 100 g, 6 ms in accordance with EN 60068-2-27

Mechanical specifications

Protection degree	IP68
Material	
Housing	PPS
Mass	1.6 g ± 0.3 g
Note	Packaging unit, 50-piece

Compliance with standards and directives

Standard conformity	
Protection degree	EN 60529
RFID	ISO/IEC 15693-1:2010, ISO/IEC 15693-2:2006, ISO/IEC 15693-3:2009, ISO/IEC 18000-3


Notes

The transponder can be read from either side.

Read/write distances

- ① IQH1-18GM-V1 ② IQH1-F61-V1 ③ IQH1-FP-V1
- ④ IQH1-F15-V1

Reading range in air IQC22-22-T9



Release date: 2014-02-13 13:17 Date of issue: 2014-02-13 261622_eng.xml