

C 143 / C 143 HD / C 143 HDM

The Basic models of the ERGOLINE Range, with a brush contact pressure from 40,3 to 41,3 gr / sq.m are suitable for any cleaning and restoration application. These models are provided with double protection against unintentional start. Satellite and planetary gearbox for high power transmission, long life and low noise level. To the characteristics that distinguish all the Wirbel single disc machines, the Ergoline units are equipped with a latest generation handle, resulted of a perfect synthesis among great sturdiness, ergonomics, safety and innovative design.


C 143	Code 00-183BL	C 143 HD	Code 00-185BL
C 143 HDM	Code 00-190BL		

TECHNICAL DATA

Working width	mm	430
Brush speed	rpm	154
Voltage	V	220 - 240
Frequency	Hz	50
Brush motor rating/HD/HDM	W	1000/1300/1600
Brush contact pressure/HD/HDM	g/cm ²	40,3/40,8/41,3
Under-ride height	mm	330
Dimensions (H x L x W)	mm	1200x542x430
Weight/HD/HDM	Kg	41/41,5/42
Power cable	m	12
Dust pick-up attachment		Yes
Noise level	dba	<54
Drive		plastic gears

SPECIAL ACCESSORIES

Suction kit for all models	00-257321
Tank Ergoline 12 l	00-330
Tynex scrubbing brush	00-246
Standard brush	00-241
Polishing brush	00-242
Carpet brush	00-243
Scrubbing disc	00-247
Carborundum disc	00-249
Pad drive board 17"	00-240
Scrubbing paper drive board 17"	00-248
Extra weight 10 kg	14-110



1. Ergonomic handle
2. Articulation of the handle
3. Satellite and planetary gearbox
4. Suitable for drive board and brushes
5. Extra weight

